

PHILIPS

Soy milk maker

Avance Collection

0.9~1.1L

5 programs

850 W

No need to filter

HD2079/05



Consume the whole bean for full nutritional value

Drink directly, no need to filter

Don't want to waste residue? Too busy to filter in the mornings? Thanks to the rapid vortex cutting super steam heating technology of the new Philips SMM, you can now get the full nutrition from every bean and drink without filtering.

Easy to use

- Five programs to enjoy your favorite drink easily

Nutrition without filtering

- Rapid cutting technology cuts beans finely, no filtering
- Super steam heating technology improves the soymilk taste

Safer and more convenient to use

- 100% food grade oil
- Double stainless steel housing, keeps warm without scalding
- Low noise
- Rotating lid design makes lifting safer & more convenient

Easy cleaning

- Easier to clean stainless steel hood

Highlights

Favorite drinks made easily



Making your favorite drink is easy by selecting the right program, including dry/soaked soymilk, five grains soymilk, rice paste, veggie/fruit juice & vegetable puree soup

Rapid cutting technology



Advanced rapid vortex cutting technology cuts beans more finely, so there's no need for filtering! What's more, 20% more dissolved protein is extracted from the soybeans*

Super steam heating technology




Super saturated steam heating technology stabilizes the temperature inside the pot, facilitating the transformation from soybean to soymilk and improving the soymilk taste.

100% food grade oil



100% food grade oil

Double stainless steel housing



Double stainless steel housing, keeps warm without scalding.

Low noise



Low noise

Rotating lid



Rotating lid design protects against leaking when dropped, making lifting safer and more convenient.

Smooth stainless steel hood



Smooth stainless steel hood is easier to clean and does not stain, making the soy milk maker more hygienic.

Specifications

Design specifications

Materials of outer housing: Stainless steel

Materials of inner housing: Stainless steel

Weight appliance: 2 kg

Technical specifications

Capacity: 1.1 L

Voltage: 220 V

Frequency: 60 Hz

Motor power: 140 W

Heating power: 850 W

Weight and dimensions

F-box dimensions: 230 x 230 x 340.5 mm

F-box weight: 2.5 kg

