

PHILIPS

Electric Pressure
Cooker

Daily Collection

Manual

5 liter

HD2105



More taste less time

The safe way to pressure cook

With intelligent cooking system, Philips Electric Pressure Cooker safely provides a variety of delicious meals in no time.

Smart and fast cooking

- Nutritional baking feature brings crispy taste
- 0-60 mins adjustable period to keep pressure
- Automatic keep warm function

Easy to operate

- Easy-to-program timer indicates the cooking progress
- Knob design for convenience

The ultimate in convenience

- Durable and non-stick inner pot
- Stainless steel outer shell for easy cleaning
- Easy to clean detachable inner lid

Safe cooking


- Auto pressure release to ensure safety
- 8 safety protection systems

Highlights

Safety auto pressure release

In case of abnormal high pressure inside the cooker, steam will be released automatically from the pressure regulator valve to ensure safety.

Durable & non-stick inner pot



Aluminum alloy inner pot is durable and offers more effective heat conduction. Special colored Whitford golden coating is anti-scratch and non-stick.

Easy-to-program timer

Easy-to-program timer indicates the cooking progress

Stainless steel outer shell



Stainless steel outer shell is exquisite and easy-to-clean

Nutritional baking feature

Nutritional baking feature brings crispy taste

0-60 mins adjustable period

Keep-pressure time can be adjusted from 0 to 60 mins based on different needs on taste and the characteristic of different food.

Knob design

Simply turn the knob to select menu listed around and set keep-pressure time.

8 safety protection systems

8 safety protection systems

Automatic keep warm function

Automatic keep warm function

Easy to clean detachable inner lid



Easy to clean detachable inner lid

Specifications

Accessories

- Ladle
- Measuring cup
- Spatula

Design specifications

- Color of control panel: Black
- Color(s): Silver
- Materials of main body: Stainless Steel

Technical specifications

- Capacity: 5 Litres / cups
- Cord length: 1.2 m
- Wattage: 900 W

