

PHILIPS

Philips multicooker

Viva Collection

5L

HD3037/79



Your new hand in your kitchen

12 functions for healthy and diverse recipes

Philips' new multicookers come with smart temperature control ensures easy cooking of favorite dishes. Top front control panel for easier operation.

Smart and automatic cooking

- 3D heating function ensuring evenly heated dishes
- Extra thick 2.0mm inner pot conducts heat evenly
- The Keep-warm function keeps dishes fresh for up to 24 hours
- Integrated microprocessor ensures easy cooking
- Dishwasher friendly & non-stick inner pot

The ultimate in convenience

- 24 hours easy-to-program preset timer
- Swing handle for easy carrying
- Detachable steam vent for easy cleaning

12 different healthy varieties

- 12 food menus for easy and more healthy varieties

Highlights

12 food menus

12 food menus for easy and more healthy varieties

24 hours easy-to-program



24 hours easy-to-program preset timer ensures dishes and meal is ready on time.

24-hour Keep-warm function



Use the Keep-warm function to keep dishes warm for long periods of up to 24 hours, whilst maintaining the food's nutrition and taste. When the cooking process finishes, the multicooker automatically switches to Keep-warm mode

3D heating function



3D heating function ensuring evenly heated dishes

Detachable steam vent




Wash the steam vent frequently to remove residual. Simply remove steam vent from the appliance top lid and clean thoroughly.

Dishwasher friendly



Dishwasher friendly & non-stick inner pot

Extra thick 2.0mm inner pot



Extra thick 2.0mm inner pot conducts heat evenly and cooks dishes tastier

Integrated microprocessor



Integrated microprocessor ensures easy cooking of favorite dishes

Swing handle for easy carrying



Convenient and safe to carry the Philips multicooker away from the kitchen, or to serve dishes in dining room

Specifications

General specifications

Reheat function for: fresh dishes instantly
Swing handle for easy carrying
Detachable power cord for convenient storage
Durable, extra thick inner pot ensures even result
Spillover prevention vent
Backup memory when power interruption
Dish washer safe inner pot

Timer mode ensures: dishes are ready when you want
Easy-to-clean non stick inner pot

Design specifications

Materials of main body: PP
Color(s): stainless steel
Color of control panel: silver

Accessories

Plastic steam tray
Measuring cup
Spatula
Ladle

Technical specifications

Voltage: 220-240 V
Frequency: 50 Hz
Wattage: 980 W
Cord length: 1.2 m
Capacity: 5/10 Litres / cups

