

PHILIPS

Multicooker

4L



HD3139/70



Fast and ease way of preparing favorite meals

Great tasting soups, meat, pasta and cakes

Philips' new multicookers come with smart temperature controls ensures easy cooking of favorite dishes. Top front control panel for easier operation.

The ultimate in convenience and ease of use

- Swing handle for easy carrying
- 24 hours preset timer ensures meals are ready on time
- 3D heating function ensuring evenly heated dishes
- Detachable steam vent for easy cleaning
- Dishwasher friendly & non-stick inner pot

Durable quality

- Extra 2.0 mm coated cast iron aluminum blended inner pot

Healthy dishes every day

- 7 automatic programs and 14 manual temperature settings
- Nutritional keep warm keeps dishes fresh for 24 hours

Highlights

24 hours preset timer



24 hours easy-to-program preset timer ensures meals are ready on time.

3D heating function



3D heating function ensuring evenly heated dishes

7 automatic programs



7 automatic programs and 14 manual temperature settings

Detachable steam vent




Wash the steam vent frequently to remove residual. Simply remove steam vent from the appliance top lid and clean thoroughly.

Dishwasher friendly



Dishwasher friendly & non-stick inner pot

Extra thick 2.0 mm coated



Extra thick 2.0 mm coated cast iron aluminum blended inner pot ensures heat is conducted uniformly ensuring dishes are always cooked evenly

Nutritional keep warm



Use the keep warm function to keep rice or dishes fresh for a longer period of time, without losing food nutrition and taste. When the cooking process is finished, the multicooker automatically switches to the keep warm mode.

Swing handle



Convenient and safe to carry the Philips rice cooker away from the kitchen, or to serve rice in dining room.

Specifications

General specifications

7 rice menu
Automatic keep-warm function
Swing handle for easy carrying
Durable, extra thick inner pot ensures even

result
Dish washer safe inner pot
Easy to clean

Accessories

Measuring cup
Spatula

Technical specifications

Voltage: 220 V
Wattage: 980 W
Cord length: 1.2 m
Capacity: 4 Litres / cups

