

PHILIPS

Mini kettle

Daily Collection

0.8 L 2400 W

1 cup indicator

White and Blue

Hinged lid



HD4608/70



Boil just what you need

This mini kettle save up to 50% energy

The unique "one cup indicator" feature of this mini kettle allows you to boil only the water you need, without taking up too much space in your kitchen. Therefore, you can easily save up to 50% energy and reduce your impact on environment

Boil what you need

- One cup indicator to boil only the water you need

Easy to experience

- Easy to read water level indicators on both sides
- Power cord winder for easy storage
- Cordless 360° pirouette base for easy lifting and placing
- Hinged lid with large opening for easy filling and cleaning
- Light indicates when the kettle is switched on

Fast boiling and easy cleaning

- Flat heating element for fast boiling and easy cleaning
- Anti-calc filter for a clean cup of water

Safe to use

- Multi safety system



asimpleswitch.com



asimpleswitch.com

Highlights

One cup indicator

Enabling consumers to boil the amount of water they need, and therefore saving of up to 50% energy and water, contributing to a better environment.

Power cord winder



The cord can be wrapped around the base, so that the kettle is easy to place in your kitchen.



Cordless 360° pirouette base

Cordless 360° pirouette base for easy lifting and placing.

Flat heating element

The stainless steel concealed element ensures fast boiling and easy cleaning.

Hinged lid

Hinged lid with large opening for easy filling and cleaning, also avoiding steam contact.

Pilot light

Elegant blue light incorporated in the on/off switch indicates when the kettle is on.

Anti-calc filter

Anti-calc filter for a clean cup of water and a cleaner kettle.

Specifications

General specifications

Product features: 360 degrees base, Automatic shut-off, Boil-dry protection, Cord storage, Flat heating element, Non-slip feet, Ergonomic grip, Lid and spout filling, Wide opening lid

Service

2-year worldwide guarantee

Technical specifications

Capacity: 0.8 L

Cord length: 0.75 m

Frequency: 50-60 Hz

Power: 900 W

Voltage: 220-240 V

Weight and dimensions

Dimensions of packaging (LxWxH): 22.5 x 22.5 x 22.5 mm

Dimensions of product (LxWxH): 15.8 x 18.5 x 22 mm

Design

Color: White and blue

Finishing

Material of main body: Polypropylene (PP)

Material switch: Polypropylene (PP)



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.