

PHILIPS

Kettle

Daily Collection

1.5 L 2400 W

Water level indicator

White

Hinged lid



HD4646/00



Fast and easy boiling

Powerful kettle, easy to clean heating element

Thanks to the flat heating element, the kettle boils water quickly and it is easy to clean. The washable anti-calc filter gives you clear water, thus clearer drinks.

Easy to experience

- Easy lid and spout filling
- Hinged lid with large opening for easy filling and cleaning
- Easy to read water level indicators on both sides
- Cord winder for easy storage
- Cordless 360° pirouette base for easy lifting and placing

Fast boiling and easy cleaning

- Flat heating element for fast boiling and easy cleaning
- Micro-mesh filter for a clean cup of water

Safe to use

- Multi safety system
- Lid knob stays cool for a safe touch

Highlights

Easy lid and spout filling

The kettle can be filled via the spout or by opening the lid.

Cord winder for easy storage



The cord can be wrapped around the base, so that the kettle is easy to place in your kitchen.

Flat heating element

The stainless steel concealed element ensures fast boiling and easy cleaning.

Cordless 360° pirouette base



Cordless 360° pirouette base for easy lifting and placing.

Multi safety system

Multi safety system against boil-dry, with auto switch off when ready

Hinged lid

Hinged lid with large opening for easy filling and cleaning, also avoiding steam contact.

Water level indicators

Easy to read water level indicators on both sides of the Philips electric kettle for left and right handed use.

Lid knob stays cool

Lid knob stays cool for a safe touch.

Micro-mesh filter



The removable micro-mesh filter on the spout restrains all scale particles with size > 200 micron and ensures that the water you put into your cup is clean.

Design specifications

Materials: Heating element: Stainless steel, Housing: Polypropylene/ ABS, Switch & toolholder: Polypropylene
Color(s): White

General specifications

Cordless
Non slip feet
Ergonomic grip
Easy spout filling
Wide opening lid
Cord storage
Automatic shut-off
Boil-dry protection
360 degrees base
Lid as well as spout filling
Flat heating element

Technical specifications

Capacity: 1.5 L
Power: 2000-2400 W
Cord length: 0.75 m
Voltage: 220-240 V
Frequency: 50-60 Hz

Dimensions

Product dimensions (WxDxH):
16.6x23x24.9 cm
Packaging dimensions (WxDxH):
28.7x18.8x23.3 cm

Service

2-year worldwide guarantee

