



### Philips Café Gourmet Coffee maker

- With glass jug
- Boil and brew system
- Black



HD5407/60

## The taste of handmade filter coffee, since 1988

with the Philips Café Gourmet coffee maker

The Philips Café Gourmet coffee machine ensures optimal coffee extraction, for a rich aroma and full flavor, thanks to the high brewing temperature of the unique Boil & Brew system, reaching 93°C or higher.

#### Great taste and aroma

- Boil & Brew system for ultimate aroma and taste
- Maintain the hot coffee temperature after brewing
- Aroma twister circulates the coffee for an optimal taste


#### Easy to experience

- Drip stop to pour a cup of coffee whenever you like
- Auto shut-off after 30 min. for energy saving and safety
- Swing filter holder for easy filling of coffee
- Cable storage for easy placement in your kitchen
- Dishwasher-safe parts for easy cleaning

# PHILIPS

# Highlights

## Aroma twister



This smart nozzle inside the jug circulates the inflowing coffee evenly through the jug for an optimal and consistent aroma, from the first to the last cup.

## Boil & Brew



The Philips coffeemaker has a unique Boil & Brew system. Water is boiled first and then flows through ground coffee. Thanks to high brewing temperature reaching 93°C or higher, this ensures the richest flavor and superior aroma for your filter coffee.

## Keep your coffee hot




After brewing your coffee, the heating plate maintains the coffee temperature, for hot and tasty coffee.

## Drip stop



The drip stop allows you to pour a cup of coffee before the full brewing cycle is finished.

## Cable storage



Spare cable can be stored in the cable compartment under the coffee maker. It enables placing the coffee maker nicely in your kitchen.

## Swing filter holder




The filter holder is opened by swinging it to the side, which makes the filling of coffee easy. The filter holder is also detachable, for easy cleaning.

## Automatic shut-off (30 min)



30 Minutes after brewing your coffee, the coffeemaker switches off automatically for energy saving and safety. This is according to EU regulation, which is applicable for all coffee makers in the EU. If you want your coffee to stay hot longer, Philips offers coffee makers with a thermal jug.

## Dishwasher-safe parts



The jug and filter holder can be easily cleaned in the dishwasher.

Coffee maker  
With glass jug Boil and brew system, Black

HD5407/60

# Specifications

## Country of origin

- Made in: Poland

## Sustainability

- Power consumption brewing: 1300 W

## Weight and dimensions

- Dimensions of product (WxDxH): 195 x 225 x 510 mm
- Weight of product: 2.3 kg
- Dimensions of packaging (WxDxH): 240 x 240 x 569 mm

## General specifications

- Coffee drinks: Drip filter coffee
- Suitable for: Ground coffee powder
- Special functions: Boil & brew
- Ease of use and comfort: Automatic shut-off, Translucent water tank, Water level indication, Drip stop
- Ease of cleaning & maintenance: Removable filter holder, Dishwasher-safe parts

## Finishing

- Material water tank: Glass
- Material of main body: Plastic

## Service

- 2-year guarantee

## Design

- Color: Black

## Accessories

- Included: Glass jug

## Technical specifications

- Cord length: 0.8 m
- Water boilers: 0
- Capacity water tank: Up to 10 cups
- Brewing time for a jug: 10 min
- Capacity water tank: 1 L
- Voltage: 220 - 240 V
- Frequency: 50 - 60 Hz
- Pump pressure: n/a bar



Issue date 2017-12-05

Version: 14.2.1

© 2017 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)