

PHILIPS

Fryer

1250g

removable bowl

with coolzone



HD6145



Enjoy the food, share the fun

Clean and long-lasting oil with cool zone system

With its cool zone system this Philips deep-fat fryer prevents food particles from burning, which keeps the oil cleaner for longer. Fried food has never been tastier! All parts except the control panel are dishwasherable for easy cleaning.

Cool zone system for cleaner, longer-lasting oil

- Prevents burnt food particles for cleaner and tastier frying

Hassle-free preparation

- Removable multi-layer filter reduces unwanted frying smells
- The digital timer allows pre-setting of frying time
- Extra large capacity for family-sized servings
- High power for quick and tasty food

Quick and easy cleaning

- All parts are dishwasherable except control panel
- Removable inner bowl for easy oil pouring and cleaning
- Additional oil container, ideal for oil filtering & storage

Safe to use

- Fryer switches automatically off 120 minutes after frying
- On/off switch for additional safety
- Rise and fall frying basket prevents oil splashes

Highlights

Cool zone system



Prevents food particles from burning. This keeps the oil cleaner, which is better for your health, and longer-lasting. Your food has never been tastier!

Removable multi-layer filter



The Philips deep fryer reduces unwanted frying smells and is dishwasherable. There is no need for replacement.

Digital timer



The digital timer allows pre-setting of frying time

Dishwashable parts



All parts are dishwasherable except control panel, for quick and easy cleaning.

Removable inner bowl



Removable inner bowl for easy oil pouring and cleaning

Additional oil container



Ideal for oil filtering and storage. Filtering keeps the oil cleaner - which is better for your health - and longer-lasting. The container can also be used for storing used oil.

Auto-shut off switch



Ultimate safety: fryer switches automatically off 120 minutes after the last frying session.

Rise and fall frying basket



Rise and fall frying basket prevents oil splashes

Specifications

General specifications

Viewing window
Cool wall exterior
Non-stick inner bowl
Automatic lid release
Detachable, hinged lid
Adjustable thermostat
Temperature light
Cord storage

Handgrips
Power-on light
Non-slip feet

Technical specifications

Power: 2400 W
Voltage: 220-240 V
Frequency: 50/60 Hz
Capacity: 1250 g
Oil content: 3.5 L
Cord length: 1.2 m

Design and finishing

Color(s): White with cornhusk yellow accents
Materials: Plastic (PP)

Weight and dimensions

Product dimensions (W x H x D):
300x265x405 mm
Weight appliance: 4.3 kg

