

PHILIPS

Deep-fat fryer

Auto-shut off

Timer



HD6155



Enjoy the food, share the fun

Large servings for a family appetite

Share the taste of fried food: this Philips deep-fat fryer can fry family-sized servings in one go! Cleaning is a breeze with the removable bowl and dishwasher parts. The additional oil container is ideal for oil filtering and storage.

Hassle-free preparation

- Extra large capacity for family-sized servings
- Removable digital timer allows pre-setting of frying time
- Removable multi-layer filter reduces unwanted frying smells

Quick and easy cleaning

- All parts are dishwasher except the housing
- Removable inner bowl for easy oil pouring and cleaning
- Additional oil container, ideal for oil filtering & storage

Safe to use

- Fryer switches automatically off 120 minutes after frying
- On/off switch for additional safety
- Rise and fall frying basket prevents oil splashes

Highlights

Removable digital timer



Allows easy pre-setting of the frying time. The timer can be removed from the fryer housing and taken along: you don't have to keep an eye on your food anymore!

Removable multi-layer filter



The Philips deep fryer reduces unwanted frying smells and is dishwasherable. There is no need for replacement.

Auto-shut off switch



Ultimate safety: fryer switches automatically off 120 minutes after the last frying session.

Rise and fall frying basket



Rise and fall frying basket prevents oil splashes

Dishwashable parts



All parts are dishwasherable except the housing

Removable inner bowl



Removable inner bowl for easy oil pouring and cleaning

Additional oil container



Ideal for oil filtering and storage. Filtering keeps the oil cleaner - which it is better for your health - and longer-lasting. The container can also be used for storing used oil.

Specifications

General specifications

Viewing window
Cool wall exterior
Non-stick inner bowl
Automatic lid release
Detachable, hinged lid
Adjustable thermostat
Temperature light
Cord storage

Handgrips
Power-on light
Non-slip feet

Technical specifications

Power: 2000 W
Voltage: 220-240 V
Frequency: 50/60 Hz
Capacity: 1300 g
Oil content: 2.5 L
Cord length: 1.2 m

Design and finishing

Color(s): White with cornhusk yellow accents
Materials: Plastic (PP)

Weight and dimensions

Product dimensions (W x H x D):
300x265x405 mm
Weight appliance: 5.1 kg

