

PHILIPS

Coffee maker

Daily Collection

With stainless steel jug

Black & metal

HD7470/20



Simply delicious coffee

With timer to wake up with fresh coffee

Enjoy the taste and aroma of freshly brewed coffee with this reliable Philips coffee maker. Wake up with the smell of fresh coffee thanks to the timer. With unbreakable stainless steel jug to last long.

Great taste and aroma

- Unbreakable stainless steel jug to last long

Designed around you

- 1,2 Liter capacity for 2 - 15 cups

Easy to experience

- Drip stop to pour a cup of coffee whenever you like
- Water level indication for easy filling
- Dishwasher-safe parts for easy cleaning
- Timer to wake up with the smell of fresh coffee
- Auto shut-off after 30 min. for energy saving and safety

Highlights

Automatic shut-off (30 min)



Auto-off

30 Minutes after brewing your coffee, the coffeemaker switches off automatically for energy saving and safety. This is according to EU regulation, which is applicable for all coffee makers in the EU. If you want your coffee to stay hot longer, Philips offers coffee makers with a thermal jug.

Stainless steel jug



Unbreakable stainless steel jug to last long.

Drip stop




The drip stop allows you to pour a cup of coffee before the full brewing cycle is finished.

Water level indication



Fill the water tank easily and precisely with the water level indication.

Dishwasher-safe parts



The jug and filter holder can be easily cleaned in the dishwasher.

Timer



Wake up with the smell of fresh coffee thanks to the timer. Prepare your coffee maker, set the time, and a fresh jug of coffee is brewed at the time you desire.

1.2 Liter capacity



This coffee maker can brew 2 up to 10 (large) / 15 (small) cups of coffee. This is maximum 1,2 liter. However, this coffee maker has a compact design and takes little place in your kitchen.

Specifications

Accessories

Included: Unbreakable steel jug

Country of origin

Made in: China

Sustainability

Power consumption brewing: 1000 W

Weight and dimensions

Dimensions of product (WxDxH): 210 x 240 x 320 mm

Weight of product: 1.42 kg

Weight incl. packaging: 3.36 kg

Finishing

Material water tank: Plastic

Material of main body: Stainless steel & plastic

Service

2-year guarantee

Design

Color: Black & Metal

General specifications

Type of display: LCD

Ease of use and comfort: Display, Preset timer, Water level indication, Automatic shut-

off, Drip stop

Ease of cleaning & maintenance: Dishwasher-safe parts

Coffee drinks: Drip filter coffee

Suitable for: Ground coffee powder

Technical specifications

Water boilers: 0

Capacity water tank: 1.2 L

Cord length: 0.85 m

Brewing time for a jug: 10 min

Voltage: 220 - 240 V

Frequency: 50 - 60 Hz

