

Coffee pod machine

Latte Select

Fresh cappuccino & latte

Deep Red

Integrated milk frother

Easy-clean function



HD7854/88



Gaggia's iconic model since 1977 with fresh frothed milk and strength select

The Philips SENSEO® Latte Select coffee machine offers you delicious coffee specialties made with fresh frothed milk. Choose from Cappuccino, Latte Macchiato, Café Latte and regular black SENSEO® coffee - all at the touch of a button.

Coffee variety for every moment

- Coffee specialities made with fresh frothed milk
- Strength select option to vary the strength of your coffee
- Range of specially developed Cabrales coffee pods

Sensational coffee quality

- Philips and Cabrales, a unique partnership
- Delicious coffee crema layer as proof of Cabrales quality

Ultimate convenience

- One cup of coffee in approx. 30 seconds
- Easy-clean button makes it easy to remove milk residues
- Adjustable cup tray for different cup sizes
- Automatic frothing system for perfectly frothed milk
- Integrated, removable milk container for more convenience

Highlights

Coffee specialities



The delicious Cappuccino, Latte Macchiato or Cortado that you can prepare with Philips Senseo Latte Select owe their rich and harmonious flavor to the perfect balance of coffee, water and fresh milk. It is time to treat your senses to the fullest!

Strength select option



Prepare your favourite cup of coffee by adjusting the strength and intensity of its taste. With the strength select option you can choose between mild, normal and strong coffee.

Automatic frothing system



The automatic frothing system of your Philips Senseo Latte Select coffee machine allows you to prepare various coffee specialties with freshly frothed milk with a rich milk foam layer

Easy-clean button



With the Easy-Clean function you can remove milk residues from your machine in a fast and comfortable way.

Wide range of coffee pods



Philips Senseo recommends range of specially developed Cabrales coffee pods. La Planta de Café, Supercabral, Colombia, Descafeinado.

Specifications

Design

Material housing: Plastic ABS

Weight and dimensions

Product dimensions (L x D x H): 210 x 340 x 360 mm

Water tank capacity: 1.2 L

Milk carafe capacity: 0.15 L

Maximum cup height: 97 - 133 mm

Max capacity in cups of coffee: Up to 8 cups

Product weight: 2.4 kg

General specifications

Ease of cleaning & maintenance:

Dishwasher-safe parts

Design specifications

Color(s): Deep Red

Service

2-year worldwide guarantee

Country of origin

Country of origin: Poland

Technical specifications

Water pressure in pump: 1 bar (filter coffee & crema)

Supported coffee types: SENSEO® coffee pods

Country of origin: Made in Poland, Designed in the Netherlands

Power: 2650 W

Voltage: 220-240 V

Frequency: 50-60 Hz

Cord length: 80 cm

Auto-off: 30 minute(s)

Black coffee brew volume: 60/80/100 ml

Cappuccino brew volume: 180 ml

Latte Macchiato brew volume: 180 ml

Cortado brewing volume: 120 ml

Dimensions

Dimensions (WxHxD): 205x350x350 mm

Packaging dimensions (WxHxD):

232x399x390 mm