

# PHILIPS

Coffee pod machine

Quadrante

Adjustable tray height



HD7860/63



## Sensational freshly brewed coffee!

### Quadrante pod coffee system

Sensational coffee comes in many shapes. Make your coffee moments truly special with SENSEO®. SENSEO® Quadrante is the easy-to-use Philips SENSEO® coffee pod system with a new design.

#### Sensational coffee

- Unique brewing system for optimal taste
- Delicious coffee crema layer as proof of Cabrales quality
- Range of specially developed Cabrales coffee pods

#### Ultimate convenience

- One button operation for total control
- One cup of coffee in approx. 30 seconds
- Automatic shut-off for less energy consumption
- Adjustable drip tray to fit your favorite cup
- Removable extra-large water reservoir for fewer refills

#### Design

- Modern machine design

# Highlights

## Unique brewing system



Unique coffee brewing system from Philips Senseo. Every cup is freshly brewed and prepared with the ultimate balance between coffee and water - a guarantee for a smooth, full taste, delicious aroma and perfect coffee temperature.

## A cup of coffee in 30 seconds



One cup of coffee in approx. 30 seconds, two cups or one mug in less than a minute.

## Automatic shut-off

With this function, your Philips Senseo coffee machine automatically switches off after 60 minutes, allowing you to save energy.

## Delicious coffee crema layer



Delicious Philips Senseo coffee crema layer as proof of premium coffee quality.

## Adjustable drip tray



By raising or lowering the drip tray you can adjust your Philips SENSEO® coffeemaker to the size of your favorite cup or mug.

## Wide range of coffee pods



Philips Senseo recommends range of specially developed Cabrales coffee pods. La Planta de Café, Supercabrales, Colombia, Descafeinado.

# Specifications

## Technical specifications

Power: 1450 W  
Voltage: 220-240 V  
Frequency: 50 - 60 Hz  
Cord length: 80 cm  
Auto-off: 30 minute(s)  
Black coffee brew volume: 80 ml

## Weight and dimensions

Product dimensions (L x D x H): 190 x 270 x 290 mm  
Water tank capacity: 1.2 L  
Maximum cup height: 97 - 117 mm  
Max capacity in cups of coffee: Up to 8 cups  
Product weight: 2.79 kg

## General specifications

Ease of cleaning & maintenance:  
Dishwasher-safe parts

## Service

2-year worldwide guarantee

## Design specifications

Color(s): Dark Stroke  
Materials: Plastic

## Country of origin

Country of origin: Poland

## Dimensions

Dimensions (WxHxD): 180x285x250 mm  
Packaging dimensions (WxHxD):  
224x328x320 mm

