

Coffee pod machine

Quadrante

Adjustable tray height

Black

2 cups included

HD7863/63



Delicious coffee at a touch, in a modern design

Enjoy the SENSEO® quality and style up your home

Style up your home with SENSEO® Quadrante coffee machine. Enjoy your coffee moments with the trusted SENSEO® brewing system, now with adjustable tray to fit your favorite cup size

Always a delicious cup of coffee

- Delicious coffee crema layer as proof of SENSEO® quality
- Unique brewing system for optimal taste and temperature
- Machine is tested >10.000 times to ensure consistent quality

Coffee variety for every moment

- Variety of coffee blends and flavors for different tastes

Fast and easy operation

- The only coffee pod maker that brews two cups at a time
- Adjustable drip tray to fit your favorite cup
- 30-minute auto shut-off for energy saving and safety
- Coffee at the touch of a button

Highlights

Delicious coffee crema layer



The fine SENSEO® coffee selection and the unique SENSEO® brewing system make sure that your perfect cup of coffee always comes with a rich and delicious coffee foam layer - proof of premium taste and quality.

One-button operation



With this coffee pod machine you can easily prepare one or two cups of coffee with the simple one button operation.

Adjustable drip tray



By raising or lowering the drip tray you can adjust your Philips SENSEO® coffeemaker to the size of your favorite cup or mug.

Variety of blends and flavors



SENSEO® offers you a large variety of coffee blends and flavors, each with its own distinctive taste to fit your personal preference.

1 or 2 cups at the same time



Prepare 1 or 2 cups of your delicious SENSEO® coffee in less than a minute.

Automatic shut-off



The SENSEO® coffee maker automatically shuts off after 30 minutes after making coffee, for energy cost saving and appliance safety.

Machine is tested >10.000 time



Philips tests their coffee makers during the development process for more than 10.000 cups of coffee. This ensures high quality and durability

Unique brewing system

At SENSEO® we know how to get the best out of the coffee bean to make great tasting single serve coffee. The operation of the SENSEO® system is simple and brilliant. Water is pumped from the boiler to the coffee pad. The hot water releases the aroma from the pad and gives a perfect cup of coffee. SENSEO® always offers you quality that you can taste.

Specifications

Weight and dimensions

Dimensions of packaging (WxDxH): 224 x 320 x 328 mm

Dimensions of product (WxDxH): 190 x 270 x 290 mm

Weight of product: 2 kg

Design

Color: Black

Sustainability

Made of recycled materials: 90% (paperwork and packaging)

Power consumption brewing: 1450 W

Power consumption stand-by: 0.35 W

Service

2-year guarantee

Technical specifications

Frequency: 50 Hz

Voltage: 220 - 240 V

Brewing time one cup: 30 sec

Brewing time two cups: <60 sec

Capacity water tank: 1.2 L

Capacity water tank: 8 cups

Cord length: 0.8 m

Max. cup height: 75 - 125 mm

Pump pressure: 1 bar

Country of origin

Made in: Poland

Finishing

Material drip tray: Metal

Material of spout: Stainless steel

General specifications

Cups at the same time: 2

Ease of cleaning & maintenance: Dishwasher-safe parts

Ease of use and comfort: Adjustable spout, Automatic shut-off, Empty water tank indication, Removable drip-tray

Accessories

Included: Cups

