

PHILIPS

Coffee pod machine

Twist

Made for SENSEO® coffee pods

Lime Yellow & White

Strength select function



HD7870/18



Brew your SENSEO® coffee the way you like it
Choose your coffee strength with intuitive control

Add style to your kitchen with the SENSEO® Twist coffee machine. You can simply choose between two recipes; long mild or short strong coffee. Plus the intuitive controls and adjustable spout give you a great coffee experience.

Always a delicious cup of coffee

- Delicious coffee crema layer as proof of SENSEO® quality
- Machine is tested >10.000 times to ensure consistent quality

Coffee variety for every moment

- Variety of coffee blends and flavors for different tastes
- Choose between 2 recipes: strong short or mild long coffee

Fast and easy operation

- The only coffee pod maker that brews two cups at a time
- Adjustable spout to fit your favorite cup
- Intuitive controls for smart guided operation
- Direct Start makes your coffee when the machine is heated up
- 15 minute auto shut-off for energy saving
- The decalcifying light reminds you when to descale



asimpleswitch.com

Highlights

Strength select function



Prepare your favorite cup of coffee by adjusting the strength and intensity of its taste. With the strength select function on your SENSEO®, you can choose between strong short and mild long coffee.

Delicious coffee crema layer



The fine SENSEO® coffee selection and the unique SENSEO® brewing system make sure that your perfect cup of coffee always comes with a rich and delicious coffee foam layer - proof of premium taste and quality.

Decalcification indicator



The SENSEO® coffee maker reminds you when to descale. Descale with SENSEO® Descal every 3 months to keep your appliance lime

scale free; ensuring: maximal in-cup volume; perfect coffee temperature, and; the appliance's durability. Do not use vinegar, since it might damage your SENSEO® appliance and affects the coffee taste.

Adjustable spout



By raising or lowering the spout you can adjust your SENSEO® coffee machine to the size of your favorite cup or mug.

Intuitive controls

Operate your Philips SENSEO® coffee machine in a modern and intuitive way with the unique and smart guided controls. The LED indicators guide you through the different functions of your coffeemaker to make your coffee experience even more convenient

Variety of blends and flavors



SENSEO® offers you a large variety of coffee blends and flavors, each with its own distinctive taste to fit your personal preference.

1 or 2 cups at the same time



Prepare 1 or 2 cups of your delicious SENSEO® coffee in less than a minute.



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Performance

Strength select: strong or regular
Brewing time 1 cup: 30 sec
Brewing time 2 cups: <60 sec

Weight and dimensions

Water tank capacity: 1 L
Packaging dimensions (LxDxH): 290 x 293 x 360 mm
Product dimensions (L x D x H): 250 x 310 x 320 mm
Product weight: 2.17 kg
Maximum cup height: up to 150 mm

Easy to use

Touch panel
2 cups at the same time
Adjustable spout
Easy-open lid
Automatic shut off time: 15 min
Brew stop
Direct start

Removable drip tray
Empty tank indication
Removable water tank

Easy to clean

Calc indicator
Dishwasher proof parts

Design

Color: Lime Yellow & White
Spray paint: lid of spout
Texture
Translucent water tank

Sustainability

Sustainability certification: Green tick
Energy consumption: 0.22 W (on stand-by), 1450 W (while brewing)
Made of recycled materials: 90% (paperwork and packaging)

Service

2-year worldwide guarantee

Technical specifications

Supported coffee types: SENSEO® coffee pods
Water pressure in pump: 1 bar (filter coffee & crema)
Country of origin: Made in Poland, Designed in the Netherlands
Water tank capacity: 6 cups / 1L
Power: 1450 W
Frequency: 50 Hz
Voltage: 220-240 V
Cord length: 80 cm

