

PHILIPS

Saeco

Manual Espresso
machine

Poemia

Classic Milk Frother

Black

HD8323/08



Authentic Italian Espresso every day

With pressurised crema filter

The Saeco manual espresso machine offers enthusiasts of traditional preparation everything for a perfect daily espresso. The patented pressurised Crema filter guarantees a long-lasting delicious crema with every use.

Authentic Italian Espresso

- Pressurised Crema filter
- 15 bar pump
- Cup holder

Simplicity and speed of use

- Ground coffee and Easy Serving Espresso (E.S.E.)
- Delicious milk froth thanks to the classic milk frother
- Ergonomic in day to day operation

Everyday use

- Long-lasting premium materials

Highlights

Pressurised Crema filter



This special crema filter guarantees a long lasting delicious crema

Ground coffee and Easy Serving



With this coffee machine you can choose between ground coffee and Easy Serving Espresso (E.S.E.) pods.

15 bar pump



High pressure ensures that the entire aroma of the ground coffee is always fully extracted

Long-lasting premium materials



The Saeco Manual Espresso machine features high-quality and durable housing material.

Cup holder



With this practical feature you can store your espresso cups and glasses right on the espresso machine - always within reach and conveniently stored without taking up space.

Ergonomic in day to day



For refilling the coffee powder or water, or emptying the filter or the drip tray, all compartments are directly accessible for maximum convenience.

Classic milk frother



This Saeco espresso machine comes with the classic milk frother that baristas call a "Pannarello". It dispenses steam and is immersed in milk to prepare gorgeous milk foam. Unleash your inner barista by preparing your delicious milk specialties the traditional way!

Specifications

Technical specifications

Boiler material: Stainless steel (Inox)

Water pressure in pump: 15 bar (perfect espresso)

Supported coffee types: E.S.E. coffee pods, Ground coffee

Country of origin: Made in China, Designed in Italy

Power: 950 W

Cord length: 80 cm

Features

Brita Filter compatible: Optional
Cup holder

Cup warmer: No

Filter holder: Pressurised "Crema"

Hot water/Steam Nozzle

Interface: Rotary Switch

Suitable for Kit Pods E.S.E.

Pannarello: Plastic

Simultaneous brewing

Service

2-year worldwide guarantee

Design

Colour: Black and Chrome

Materials and finishing: ABS

Weight and dimensions

Water tank capacity: 1.25 l

Maximum cup height: 75 mm

Product weight: 4 kg

Product dimensions (L x D x H): 200 x 265 x 297 mm

