

# PHILIPS

## Saeco

Manual Espresso  
machine

Poemia

Classic Milk Frother

Stainless steel



HD8327/09



## Authentic Italian Espresso every day With pressurised crema filter

The Saeco manual espresso machine offers enthusiasts of traditional preparation everything for a perfect daily espresso. The patented pressurised filter Crema guarantees a long-lasting delicious crema with every use.

### Authentic Italian Espresso

- Pressurised Crema filter holder
- 15 bar pump
- Cup warmer

### Simplicity and speed of use

- Suitable for ground coffee and pods
- Delicious milk froth thanks to the classic milk frother
- Ergonomic in day to day operation

### Everyday use

- stainless steel espresso machine

# Highlights

## Pressurised Crema filter



This special Crema filter guarantees a long-lasting, delicious Crema — whatever coffee blend you may choose.

## Ground coffee and pods



For your convenience you can choose between ground coffee and pods

## 15 bar pump



High pressure ensures that the entire aroma of the ground coffee is always fully extracted

## Cup warmer



This feature allows you to not only store your espresso cups and glasses right on the espresso machine, it also pre-heats them letting the aroma unfold even better and guaranteeing a long-lasting crema

## Ergonomic in day to day



For refilling the coffee powder or water, or emptying the filter or the drip tray, all compartments are directly accessible for maximum convenience.

## Full stainless steel



premium material, which is long lasting and easy to clean

## Classic milk frother



This Saeco espresso machine comes with the classic milk frother that baristas call a “Pannarello”. It dispenses steam and is immersed in milk to prepare gorgeous milk foam. Unleash your inner barista by preparing your delicious milk specialties the traditional way!

# Specifications

## Technical specifications

**Boiler material:** Stainless steel (Inox)

**Water pressure in pump:** 15 bar (perfect espresso)

**Supported coffee types:** Coffee pods, Ground coffee

**Country of origin:** Made in China, Designed in Italy

**Power:** 950 W

**Cord length:** 80 cm

## Features

**Brita Filter compatible:** Optional  
**Cup warmer**

**Filter holder:** Pressurised "Crema"

**Hot water/Steam Nozzle**

**Interface:** Rotary Switch

**Suitable for pods**

**Pannarello:** Stainless Steel

**Simultaneous brewing**

## Service

**2-year worldwide guarantee**

## Design

**Colour:** Stainless Steel

**Materials and finishing:** Stainless Steel

## Weight and dimensions

**Water tank capacity:** 1.25 l

**Maximum cup height:** 75 mm

**Product weight:** 4 kg

**Product dimensions (L x D x H):** 200 x 265 x 297 mm

