

PHILIPS

Saeco

Manual Espresso
machine

Poemia

Stainless Steel



HD8327/91



Authentic Italian Espresso every day With pressurized crema filter

Saeco Poemia coffee machine offers enthusiasts of traditional preparation everything for a perfect daily espresso. The patented pressurized filter Crema guarantees a long lasting delicious crema, at every use.

Authentic Italian Espresso

- Pressurized Crema filter holder
- 15 bar pump
- Cup warmer

Simplicity and speed of use

- Suitable for ground coffee and pads
- Delicious milk froth thanks to the classic milk frother
- Ergonomic in day by day operations

Every day use

- Stainless steel espresso machine

Highlights

Pressurized Crema filter



This special Crema filter guarantees a long-lasting, delicious Crema – whatever coffee blend you may choose.

Ground coffee and pads



For your convenience you can choose between ground coffee pads

15 bar pump



High pressure ensures that the ground coffee entire aroma is always fully extracted

Cup warmer



This feature allows you to not only store your espresso cups and glasses right on the espresso machine, it also pre-heats them letting the aroma unfold even better and guaranteeing a long-lasting crema

Ergonomic in day by day



Refilling coffee powder or water, emptying the filter or the drip tray. All compartments are directly accessible for maximum convenience.

Full stainless steel



Premium material for long lasting machine and easy to clean.

Classic milk frother



This Saeco espresso machine comes with the classic milk frother that baristas call a "Pannarello". It dispenses steam and is immersed in milk to prepare gorgeous milk foam. Unleash your inner barista by preparing your delicious milk specialties the traditional way!

Specifications

Technical specifications

Boiler material: Aluminium

Water pressure in pump: 15 bar (perfect espresso)

Supported coffee types: Coffee pods, Ground coffee

Country of origin: Made in China, Designed in Italy

Power: 950 W

Cord length: 80 cm

Features

Brita Filter compatible: Optionable
Cupholder

Filterholder: Pressurized "Crema"

Hot water / Steam Nozzle

Interface: Rotary Switch

Suitable for pods

Pannarello: Stainless Steel

Simultaneous brewing

Service

2-year worldwide guarantee

Design

Colour: Stainless Steel

Materials and finishing: Stainless Steel

Weight and dimensions

Water tank capacity: 1.25 L

Maximum cup height: 75 mm

Product weight: 4 kg

Product dimensions (L x D x H): 200 x 265 x 297 mm

