

PHILIPS

Saeco

Super-automatic
espresso machine

Xsmall

Brews 2 coffee varieties

Classic Milk Frother

Black

5 step adjustable grinder



HD8743/11



Taste the aroma of your favorite coffee beans one touch bean to cup espresso

Whatever coffee you wish to try next, the Saeco Xsmall will grind the beans fresh on the spot at the touch of a button. It comes equipped with a steam pipe to add a touch of milk froth pleasure to all your fresh coffee drinks.

Authentic Italian coffee perfection

- Coffee without burnt taste thanks to 100% ceramic grinders

Set the beverages to suit your taste

- Save your favorite coffee length
- Play with the coffee's richness with our adjustable grinders

Ease of cleaning and maintaining

- Always a clean machine thanks to automatic circuit cleaning
- Easy cleaning thanks to removable brewing group



asimpleswitch.com

Highlights

Automatic circuit cleaning



Saeco designed this espresso machine to automatically clean its coffee circuit with water upon starting up or switching off of the machine, this delivers a great, fresh taste with each cup of coffee.

100% ceramic grinders



This espresso machine is equipped 100% ceramic grinders. Saeco uses ceramic grinders because of their consistent grind without overheating the coffee bean for an impeccable espresso. Ceramic also ensures long-lasting performance and a totally silent operation.

Saves your coffee length



You will always get a perfect cup of espresso brewed according to your personal preference thanks to our memo function which allows you

to adjust the coffee length to suit your taste. Enjoy a superb coffee drink with just the press of a button.

5 step adjustable grinders



Different coffee blends require different levels of granularity for the full flavor to unfold. The grind granularity of this espresso machine can be adjusted in 5 settings, from the finest grind, for a full bodied espresso, to the coarsest, for a lighter coffee.

Removable brewing group



The brewing group, a Saeco invention, is the heart of our espresso machines, ensuring automation. The brewing group is, depending on the model, easily accessible from the front or side. It can be removed effortlessly for easily cleaning by rinsing under the tap ensuring maximum hygiene.

Specifications

Design

Color: Black & silver

Finishing

Material boiler: Stainless steel
Material drip tray: Stainless steel
Material of main body: Plastic
Material of spout: Plastic

Country of origin

Made in: Romania

General specifications

Suitable for: Whole coffee beans
Cups at the same time: 2
Ease of cleaning & maintenance: Automatic rinse cycle, Removable brewing group
Ease of use and comfort: Removable drip-tray, Removable water tank
Special functions: Pre-brewing
Coffee drinks: Espresso, hot water

Service

2-year guarantee

Sustainability

Power consumption brewing: 1400 W

Technical specifications

Capacity bean container: 180 gr
Capacity waste container: 8 servings
Capacity water tank: 1 L
Cord length: 0.8 m
Frequency: 50 Hz
Max. cup height: 95 mm
Pump pressure: 15 bar
Voltage: 230 V
Water boilers: 1

Weight and dimensions

Dimensions of product (WxDxH): 420 x 325 x 295 mm
Weight of product: 7.2 kg



[asimpleswitch.com](https://www.asimpleswitch.com)

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

