



Philips Saeco Intelia
Super-automatic espresso
machine

Brews 7 coffee varieties

Classic Milk Frother

Black

5 step adjustable grinder



HD8751/11

One touch Espresso and Cappuccino

With ceramic coffee bean grinders for better taste

Only the Saeco Intelia super-automatic espresso machine offers you the perfect Espresso experience, easy to use, easy to customize, easy to clean. Prepare Cappuccino, Latte Macchiato, Espresso or hot water: everything is possible.

Advanced technology designed for coffee perfection

- Fine-tune the coffee's richness with 5 grinder settings
- Extract maximum flavor with the 100% ceramic grinders
- Velvety milk foam with the Classic Milk Frother


High comfort is part of the experience

- The fully removable brewing group can be cleaned in no time



asimpleswitch.com

 **Saeco**



Highlights

5-steps adjustable grinders



When it comes to the fineness of the grind, this machine never fails to satisfy. Different coffee blends require different levels of granularity for the full flavor to unfold. So the grind granularity of this machine has five adjustable settings - from the finest grind for a full-bodied espresso, to the coarsest for a lighter coffee.

100% Ceramic grinders



The robust 100% ceramic grinders guarantee a moment of pure coffee indulgence for years to come. The ceramic material creates the ideal grind, which allows the water to flow through steadily, extracting the purest essence of the beans. And unlike other 'regular' grinders, the ceramic material

prevents the coffee from overheating and tasting burnt.

Removable brewing group



Efficiency and ease of use were key inspirations when Saeco invented the first brewing group 30 years ago. And to this day, it still proves to be an inspired, resolute piece of technology. As always, it's so simple to clean – just remove it and wash it under the tap for a few seconds, then re-insert it just as easily.

Classic Milk Frother



The Classic Milk Frother is for those who love to assume the role of master craftsman, and it's just easy. Within seconds you can create a rich, silky layer of foam - the crowning glory of your coffee.

Specifications

Country of origin

- Made in: Europe

Sustainability

- Power consumption brewing: 1900 W

Finishing

- Material boiler: Stainless steel (Inox)
- Material water tank: Plastic
- Material panarello: Plastic
- Material of main body: Plastic
- Material drip tray: Stainless steel
- Material of spout: Plastic

Service

- 2-year guarantee

General specifications

- Type of carafe: Basic carafe
- Type of display: LCD
- Coffee drinks: Espresso, Cappuccino, hot water, Café Crème, frothed milk, Espresso Macchiato, Latte Macchiato
- Compatible coffee serving: Whole coffee beans, ground coffee powder
- Cups at the same time: 2
- Type of boiler: Quick heat boiler
- Ease of cleaning & maintenance: Automatic rinse cycle, AquaClean filter compatible, Automatic descaling cycle, Removable brewing group, Optional Brita water filter
- Special functions: Ceramic grinder, Steam option, Hot water option, Pre-brewing, Manual milk frother Pannarello
- Ease of use and comfort: Display, Adjustable spout, Automatic shut-off, Automatic stand-by

Technical specifications

- Pump pressure: 15 bar
- Voltage: 230 V
- Frequency: 50 Hz
- Capacity water tank: 1.5 l
- Max. cup height: 130 mm
- Capacity bean container: 300 gr
- Cord length: 0.8 m
- Water boilers: 1
- Capacity waste container: 10 servings
- Pump pressure: 15 bar

Weight and dimensions

- Dimensions of product (WxDxH): 256 x 440 x 340 mm
- Weight of product: 8.9 kg

Design

- Color: Black



Issue date 2016-07-25

Version: 13.1.1

EAN: 08 71010 35411 34

© 2016 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com