

PHILIPS

Saeco

Super-automatic
espresso machine

Intelia

Brews 7 coffee varieties

Classic Milk Frother

Black

5 step adjustable grinder



HD8751/19



One touch espresso and coffee

With ceramic coffee bean grinders for better taste

Only the Saeco Intelia super-automatic espresso machine offers you the perfect Espresso experience, easy to use, easy to customize, easy to clean. Prepare Cappuccino, Latte Macchiato, Espresso or hot water: everything is possible.

Advanced technology designed for coffee perfection

- Fine-tune the coffee's richness with 5 grinder settings
- 20,000 cups of finest coffee with durable ceramic grinders
- Velvety milk foam with the Classic Milk Frother

High comfort is part of the experience

- The fully removable brewing group can be cleaned in no time



asimpleswitch.com

Highlights

5-steps adjustable grinders



When it comes to the fineness of the grind, this machine never fails to satisfy. Different coffee blends require different levels of granularity for the full flavor to unfold. So the grind granularity of this machine has five adjustable settings – from the finest grind for a full-bodied espresso, to the coarsest for a lighter coffee.

100% Ceramic grinders



Our grinders are made of high-tech ceramic: exceptionally hard and precise. Fresh beans are gently ground, without risk of overheating: extracting all the best flavors and aroma, delivering a superior coffee taste for at least 20,000 cups.

Removable brewing group



Efficiency and ease of use were key inspirations when Saeco invented the first brewing group 30 years ago. And to this day, it still proves to be an inspired, resolute piece of technology. As always, it's so simple to clean – just remove it and wash it under the tap for a few seconds, then re-insert it just as easily.

Classic Milk Frother



The Classic Milk Frother is for those who love to assume the role of master craftsman, and it's just easy. Within seconds you can create a rich, silky layer of foam – the crowning glory of your coffee.



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Technical specifications

Pump pressure: 15 bar
Capacity bean container: 300 gr
Capacity waste container: 10 servings
Max. cup height: 130 mm
Brewing time one cup: 45 (espresso) to 100 (long coffee) sec
Water boilers: 1
Voltage: 230 V
Frequency: 50 Hz
Cord length: 0.8 m
Capacity water tank: 1.5 L

Sustainability

Power consumption brewing: 1900 W

General specifications

Cups at the same time: 2
Suitable for: Whole coffee beans, ground coffee powder
One touch variety: 3
Coffee strength settings: 3

Temperature settings: 3
Grinder settings: 5
Type of boiler: Quick heat boiler
Type of display: LCD
Special functions: Ceramic grinder, Manual milk frother Pannarello, Steam option, Pre-brewing, Hot water option
Customizing per drink: Adjustable coffee strength, Adjustable temperature, Adjustable cup volume
Ease of use and comfort: Removable spout, Removable drip-tray, Automatic stand-by, Automatic shut-off
Ease of cleaning & maintenance: Automatic de-scaling cycle, Removable brewing group, Optional Brita water filter, Automatic rinse cycle, AquaClean filter compatible
Coffee drinks: Espresso, Cappuccino, hot water, Cafè Crème, frothed milk, Espresso Macchiato, Latte Macchiato

Finishing

Material boiler: Stainless steel (Inox)
Material drip tray: Stainless steel
Material of main body: Plastic
Material panarello: Plastic
Material water tank: Plastic

Country of origin

Made in: Europe

Service

2-year guarantee

Weight and dimensions

Weight of product: 8.9 kg
Dimensions of product (WxDxH): 256 x 340 x 440 mm

Design

Color: Black

