

PHILIPS

Saeco

Super-automatic
espresso machine

Intelia

Brews 7 coffee varieties

Automatic Milk Frother

Stainless steel

5 step adjustable grinder



HD8752/89



One touch espresso and creamy milk froth With Saeco's ultimate automatic milk frother

Only the Saeco Intelia Class super-automatic espresso machine offers you the perfect espresso experience: easy to use, easy to clean and protected by premium, long lasting stainless steel.

Advanced technology designed for coffee perfection

- Fine-tune the coffee's richness with 5 grinder settings
- 20,000 cups of finest coffee with durable ceramic grinders
- Velvety froth at one touch with the Automatic Milk Frother

High comfort is part of the experience

- The fully removable brewing group can be cleaned in no time

A variety of coffees customized to your taste

- The strength selection remembers just how strong you like it

Ease of cleaning and maintaining

- Always a clean machine thanks to auto-clean and descaling
- Easy cleaning thanks to dishwasher-safe parts
- Extra robust, extra accessorized
- Self explanatory color coded user interface



asimpleswitch.com

Highlights

Extra robust and accessorized



Extra robust, extra accessorized

Dishwasher-safe parts



For your convenience, you can put the Saeco's drip tray and milk frother or milk carafe in the dishwasher. This will save time and ensure a hygienic cleaning.

Auto cleaning and descaling



Saeco designed this espresso machine to automatically clean its coffee circuit with water upon starting up or switching off of the machine, this delivers a great, fresh taste with each cup of coffee. Regular descaling prolongs your espresso machine's life. This machine will not only prompt when descaling is needed, the automated descaling process will start on your machine and guides you with clear on-screen messages when you have to intervene. Descaling has never been so easy!

Color coded user interface

Enjoy direct and clear interaction thanks to the self-explanatory icons display. For maximum convenience the icons are colored according to

the traffic light colors: Red requires action, Yellow means the coffee machine is "busy" (like heating up). Green is ready to use.

5-steps adjustable grinders




When it comes to the fineness of the grind, this machine never fails to satisfy. Different coffee blends require different levels of granularity for the full flavor to unfold. So the grind granularity of this machine has five adjustable settings – from the finest grind for a full-bodied espresso, to the coarsest for a lighter coffee.

100% Ceramic grinders



Our grinders are made of high-tech ceramic: exceptionally hard and precise. Fresh beans are gently ground, without risk of overheating: extracting all the best flavors and aroma, delivering a superior coffee taste for at least 20,000 cups.

Removable brewing group



Efficiency and ease of use were key inspirations when Saeco invented the first brewing group 30 years ago. And to this day, it still proves to be an inspired, resolute piece of

technology. As always, it's so simple to clean – just remove it and wash it under the tap for a few seconds, then re-insert it just as easily.

Memo Function



Once you've chosen your ideal strength from the 5 different settings, you can easily save it with the Memo Function, as well your desired length and temperature. Then every cup in the future will be customised exactly to your taste. You'll never have to remind it again, unlike the local barista.

Automatic Milk Frother



The Automatic Milk Frother will deliver your coffee's crowning glory at the touch of a button. Within seconds it will be topped with a silky, milk layer of the finest consistency – the ultimate lure for all cappuccino lovers.



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Technical specifications

Pump pressure: 15 bar
Capacity bean container: 300 gr
Capacity waste container: 10 servings
Max. cup height: 130 mm
Brewing time one cup: 45 (espresso) to 100 (long coffee) sec
Water boilers: 1
Voltage: 230 V
Frequency: 50 Hz
Cord length: 0.8 m
Capacity water tank: 1.5 L

Sustainability

Power consumption brewing: 1850 W

General specifications

Cups at the same time: 2
Suitable for: Whole coffee beans, ground coffee powder
One touch variety: 3
Coffee strength settings: 3

Temperature settings: 3
Grinder settings: 5
Type of boiler: Quick heat boiler
Type of display: LCD
Special functions: Ceramic grinder, Manual milk frother Pannarello, Steam option, Pre-brewing, Hot water option, Automatic milk frother
Customizing per drink: Adjustable coffee strength, Adjustable temperature, Adjustable cup volume
Ease of use and comfort: Adjustable spout, Removable drip-tray, Automatic stand-by, Automatic shut-off
Ease of cleaning & maintenance: Automatic de-scaling cycle, Removable brewing group, Optional Brita water filter, Automatic rinse cycle, AquaClean filter compatible
Coffee drinks: Espresso, Cappuccino, hot water, Cafè Crème, frothed milk, Espresso Macchiato, Latte Macchiato

Finishing

Material boiler: Stainless steel (Inox)
Material drip tray: Stainless steel
Material of main body: Stainless steel & plastic
Material water tank: Plastic

Country of origin

Made in: Europe

Service

2-year guarantee

Weight and dimensions

Weight of product: 8.9 kg
Dimensions of product (WxDxH): 256 x 340 x 440 mm

Design

Color: Stainless steel & black

