



Philips Saeco Intelia
Super-automatic espresso
machine

Brews 7 coffee varieties

Integrated milk jug & frother
Black
5 step adjustable grinder



HD8753/11

One touch Espresso and Cappuccino

With Saeco's latest Latte Perfetto technology

Only the Saeco Intelia super-automatic espresso machine offers you the perfect Espresso experience, easy to use, easy to customize, easy to clean. Prepare perfect Cappuccino or Espresso with just a touch of a button.

Advanced technology designed for coffee perfection

- Fine-tune the coffee's richness with 5 grinder settings
- Extract maximum flavor with the 100% ceramic grinders

High comfort is part of the experience

- The fully removable brewing group can be cleaned in no time


A variety of coffees customized to your taste

- The strength selection remembers just how strong you like it



asimpleswitch.com

 **Saeco**



Highlights

5-steps adjustable grinders



When it comes to the fineness of the grind, this machine never fails to satisfy. Different coffee blends require different levels of granularity for the full flavor to unfold. So the grind granularity of this machine has five adjustable settings - from the finest grind for a full-bodied espresso, to the coarsest for a lighter coffee.

100% Ceramic grinders



The robust 100% ceramic grinders guarantee a moment of pure coffee indulgence for years to come. The ceramic material creates the ideal grind, which allows the water to flow through steadily, extracting the purest essence of the beans. And unlike other 'regular' grinders', the ceramic material prevents the coffee from overheating and tasting burnt.

Removable brewing group



Efficiency and ease of use were key inspirations when Saeco invented the first brewing group 30 years ago. And to this day, it still proves to be an inspired, resolute piece of technology. As always, it's so simple to clean – just remove it and wash it under the tap for a few seconds, then re-insert it just as easily.

Memo Function



Once you've chosen your ideal strength from the 5 different settings, you can easily save it with the Memo Function, as well your desired length and temperature. Then every cup in the future will be customised exactly to your taste. You'll never have to remind it again, unlike the local barista.

Specifications

Technical specifications

- Pump pressure: 15 bar
- Capacity milk carafe: 500 L
- Capacity bean container: 300 gr
- Capacity waste container: 10 servings
- Max. cup height: 130 mm
- Brewing time one cup: 45 (espresso) to 100 (long coffee) sec
- Water boilers: 1
- Voltage: 230 V
- Frequency: 50 Hz
- Cord length: 0.8 m
- Capacity water tank: 1.5 L

Sustainability

- Power consumption brewing: 1900 W

General specifications

- Cups at the same time: 2
- Compatible coffee serving: Whole coffee beans, ground coffee powder
- One touch variety: 7
- Coffee strength settings: 3
- Temperature settings: 3
- Grinder settings: 5
- Type of carafe: Basic carafe
- Type of boiler: Quick heat boiler
- Type of display: LCD
- Special functions: Ceramic grinder, Integrated carafe, Pre-brewing, Hot water option
- Customizing per drink: Adjustable coffee strength, Adjustable temperature, Adjustable cup volume
- Ease of use and comfort: Display, Adjustable spout, Removable drip-tray, Automatic stand-by, Automatic shut-off
- Ease of cleaning & maintenance: Automatic descaling cycle, Removable brewing group, Optional Brita water filter, Automatic rinse cycle
- Coffee drinks: Espresso, Cappuccino, hot water, Café Crème, frothed milk, Espresso Macchiato, Latte Macchiato

Finishing

- Material boiler: Stainless steel (Inox)
- Material drip tray: Stainless steel
- Material of main body: Stainless steel & plastic
- Material water tank: Plastic

Country of origin

- Made in: Europe

Service

- 2-year guarantee

Weight and dimensions

- Weight of product: 8.9 kg
- Dimensions of product (WxDxH): 256 x 440 x 340 mm

Design

- Color: Black

