



Saeco Moltio Super-automatic espresso machine

- Brews 7 coffee varieties
- Integrated milk jug & frother
- Pearl Silver
- 5 step adjustable grinder

HD8778/11



Every moment deserves its perfect coffee flavor

Changing coffee beans is now one click away

Moltio, a unique masterpiece crafted to offer a tailored taste experience. Thanks to our exclusive bean switcher, preparing the right coffee treat that always matches your mood or the moment of the day will be as easy as a click

Advanced technology designed for coffee perfection

- Fine-tune the coffee's richness with 5 grinder settings
- 20,000 cups of finest coffee with durable ceramic grinders

High comfort is part of the experience

- The fully removable brewing group can be cleaned in no time

A variety of coffees customized to your taste

- The strength selection remembers just how strong you like it

PHILIPS

Saeco, a Philips brand

 **Saeco**



Highlights

5-steps adjustable grinders



When it comes to the fineness of the grind, this machine never fails to satisfy. Different coffee blends require different levels of granularity for the full flavor to unfold. So the grind granularity of this machine has five adjustable settings - from the finest grind for a full-bodied espresso, to the coarsest for a lighter coffee.

100% Ceramic grinders



Our grinders are made of high-tech ceramic: exceptionally hard and precise. Fresh beans are gently ground, without risk of overheating: extracting all the best flavors and aroma, delivering a superior coffee taste for at least 20,000 cups.

Removable brewing group



Efficiency and ease of use were key inspirations when Saeco invented the first brewing group 30 years ago. And to this day, it still proves to be an inspired, resolute piece of technology. As always, it's so simple to clean – just remove it and wash it under the tap for a few seconds, then re-insert it just as easily.

Memo Function



Once you've chosen your ideal strength from the 5 different settings, you can easily save it with the Memo Function, as well your desired length and temperature. Then every cup in the future will be customised exactly to your taste. You'll never have to remind it again, unlike the local barista.

Specifications

Technical specifications

- Pump pressure: 15 bar
- Capacity milk carafe: 500 L
- Capacity bean container: 290 gr
- Capacity waste container: 15 servings
- Max. cup height: 142 mm
- Brewing time one cup: 45 (espresso) to 100 (long coffee) sec
- Water boilers: 1
- Voltage: 230 V
- Frequency: 50 Hz
- Cord length: 0.8 m
- Capacity water tank: 1.9 L

Sustainability

- Power consumption brewing: 1850 W

General specifications

- Cups at the same time: 2
- Suitable for: Whole coffee beans, ground coffee powder
- One touch variety: 7
- Coffee strength settings: 5
- Temperature settings: 3
- Grinder settings: 5
- Type of carafe: Basic carafe
- Type of boiler: Quick heat boiler
- Type of display: LCD
- Special functions: Ceramic grinder, Integrated carafe, Pre-brewing
- Customizing per drink: Adjustable coffee strength, Adjustable temperature, Adjustable cup volume
- Ease of use and comfort: Display, Removable spout, Removable drip-tray, Automatic stand-by, Automatic shut-off
- Ease of cleaning & maintenance: Automatic descaling cycle, Removable brewing group, Optional Brita water filter, Automatic carafe cleaning, Automatic rinse cycle
- Coffee drinks: Espresso, Cappuccino, hot water, Café Crème, frothed milk, Espresso Macchiato, Latte Macchiato

Finishing

- Material boiler: Stainless steel (Inox)
- Material drip tray: Stainless steel
- Material of main body: Plastic
- Material water tank: Plastic

Country of origin

- Made in: Italy

Service

- 2-year guarantee

Weight and dimensions

- Weight of product: 8.5 kg
- Dimensions of product (WxDxH): 256 x 470 x 350 mm

Design

- Color: Silver

