

PHILIPS

Super-automatic
espresso machine

3000 Series

3 Beverages

Classic Milk Frother

Black



HD8821/01



Your favorite coffee always just one touch away
With unique 100% ceramic grinder for perfect taste

Get your perfect espresso, extracting the best out of each fresh bean thanks to the 100% ceramic grinders that don't overheat coffee beans. Your hot frothed milk is exactly how you want it thanks to the classic milk frother.

A variety of coffees customized to your taste

- Enjoy 3 coffees at your fingertips
- Delicious milk froth thanks to the classic milk frother
- Adjust the length and 5 grinder settings
- Enjoy 2 cups at the same time with Double Cup function
- Adjust and store your personal user profile

Your fresh coffee experience

- 20,000 cups of finest coffee with durable ceramic grinders
- Adjust your coffee spout to fit any cup
- Coffee at the perfect temperature with our Thermoblock

Enjoy your coffees every day with no hassle

- Designed to maximize capacities in a compact footprint
- Easy cleaning thanks to fully removable brew group
- Enjoy a great coffee with Auto-Rinse & guided descaling

Highlights

100% ceramic grinders



Our grinders are 100% pure ceramic: extremely hard and precise, so you can enjoy fresh aromatic coffee, for at least 20.000 cups.

3 aromatic coffees



Enjoy your favourite coffees for your special moments. Whether you crave for an espresso, a coffee or a milk based recipe, your fully-automatic espresso machine delivers a perfect in-cup result with no hassle and in no time!

Adjustable coffee spout



The adjustable spout on our espresso machines will fit every cup and thus prevents the coffee splashing or cooling down while pouring in your cup. This way your espresso is always served at the right temperature while maintaining a clean machine.

Classic milk frother



The Classic Milk Frother dispenses steam, allowing you to easily prepare silky smooth milk froth for your cappuccino. What's more? With only two parts, the Classic Milk Frother is also easy to clean.

Customize your coffees




Adjust the length and 5 grinder settings

Double Cup

Enjoy and share your favorite coffee thanks to the double cup function

High capacity & compact design



Enjoy more room and go longer without refill thanks to the high-capacity bean, water, and waste containers in a super-compact design. This smart, super-automatic machine provides you with maximum convenience and top notch performance thanks to a large capacity water tank, bean and waste container.

Thermoblock



The Thermoblock ensures a hot coffee and cappuccino for your family always at the perfect temperature. The secret is in its light aluminum and stainless steel body, which can reach hot temperatures, fast.

Removable brew group



The brew group is the heart of every fully automatic coffee machine, and should be cleaned regularly. The removable brew group allows you to clean it thoroughly just by rinsing it under the tap.

User Profiles



Store the length of any coffee beverage according to your personal taste. You will be able to drink espresso, coffee and all other beverages always as you prefer, at the touch of a button.

Specifications

Customization

Aroma Strength Settings: No
Coffee Length: Adjustable
Grinder Settings: 5
Pre Brew Aroma control: No
User Profiles: 1

General specifications

Milk Solution: Classic Milk Frother
User Interface: LED Buttons

Other features

Auto-Rinse & Guided descaling
Main Switch ON / OFF button
Quick Heat Boiler
Removable brew group

Technical specifications

Capacity waste container: 15 servings
Frequency: 50 Hz
Max. cup height: 152 mm
Voltage: 230 V
Color & Finishing: Black
Cord length: >100 cm
Filter compatibility: Brita Intenza

Waste container: Frontal access

Water tank: Access from the top

Weight of product: 7.2 kg

Product dimensions: 215 x 330 x 429 mm

Coffee bean capacity: 250 g

Capacity water tank: 1.8 L

Variety

Beverages: Espresso, Hot water, Coffee

Coffee Powder Option: No

Double Cup

Milk Double Cup: No

