

PHILIPS

Super-automatic
espresso machine

3000 Series

4 Beverages

Automatic Milk Frother

Black



HD8825/09



Your favorite coffee always just one touch away
With unique 100% ceramic grinder for perfect taste

Get your perfect espresso, extracting the best out of each fresh bean thanks to the 100% ceramic grinders that don't overheat coffee beans. Your frothed milk is a one-touch job, thanks to the automatic milk frother.

A variety of coffees customized to your taste

- Enjoy 4 coffees at your fingertips
- Velvety froth at one touch with the Automatic Milk Frother
- Adjust the length and 5 grinder settings
- Adjust and store your personal user profile

Your fresh coffee experience

- 20,000 cups of finest coffee with durable ceramic grinders
- Smooth milk foam from the carafe frother
- Coffee at the perfect temperature with our Thermoblock

Enjoy your coffees every day with no hassle

- Designed to maximize capacities in a compact footprint
- Easy cleaning thanks to fully removable brew group
- Enjoy a great coffee with Auto-Rinse & guided descaling

Highlights

100% ceramic grinders



Our grinders are 100% pure ceramic: extremely hard and precise, so you can enjoy fresh aromatic coffee, for at least 20.000 cups.

4 aromatic coffees



Enjoy your favourite coffees for your special moments. Whether you crave for an espresso, a coffee or a milk based recipe, your fully-automatic machine delivers a perfect in-cup result with no hassle and in no time!

Automatic Milk Frother




Preparing a velvety cappuccino is easy thanks to the Automatic Milk Frother. The milk frother, which baristas also call "cappuccinatore", will draw the milk directly from a carton or jug, froth it automatically and dispensing it into your cup with a constant flow of milk without any splashing.

Customize your coffees



Adjust the length and 5 grinder settings

High capacity & compact design



Enjoy more room and go longer without refill thanks to the high-capacity bean, water, and waste containers in a super-compact design. This smart, super-automatic machine provides you with maximum convenience and top notch performance thanks to a large capacity water tank, bean and waste container.

Latte Perfetto Technology



Every coffee you prepare will be topped with a silky, milk layer that beckons the taste buds. The milk carafe froths the milk twice, then pours a splash free creamy layer into your cup at just the right temperature. The carafe can also be stored conveniently in the fridge and it is incredibly hygienic.

Thermoblock



The Thermoblock ensures a hot coffee and cappuccino for your family always at the perfect temperature. The secret is in its light aluminum and stainless steel body, which can reach hot temperatures, fast.

Removable brew group



The brew group is the heart of every fully automatic coffee machine, and should be cleaned regularly. The removable brew group allows you to clean it thoroughly just by rinsing it under the tap.

User Profiles



Store the length of any coffee beverage according to your personal taste. You will be able to drink espresso, coffee and all other beverages always as you prefer, at the touch of a button.

Specifications

General specifications

Milk Solution: Automatic milk frother
User Interface: LED Buttons

Technical specifications

Capacity waste container: 15 servings
Frequency: 50 Hz
Max. cup height: 152 mm
Voltage: 230 V
Color & Finishing: Black
Cord length: >100 cm
Filter compatibility: Brita Intenza
Waste container: Frontal access

Water tank: Access from the top
Weight of product: 7.2 kg
Product dimensions: 215 x 330 x 429 mm
Coffee bean capacity: 250 g
Capacity water tank: 1.8 L

Customization

Aroma Strength Settings: No
Grinder Settings: 5
Pre Brew Aroma control: No
User Profiles: 1
Coffee and Milk Length: Adjustable

Variety

Beverages: Espresso, Espresso Lungo, Hot water, Milk froth
Coffee Powder Option: No
Double Cup
Milk Double Cup: No

Other features

Auto-Rinse & Guided descaling
Main Switch ON / OFF button
Quick Heat Boiler
Removable brew group

