



## Saeco Incanto Super-automatic espresso machine

- 6 Beverages
- Integrated milk carafe
- PianoBlack
- AquaClean

HD8916/09



Elegant design. Impressive coffee quality.

Delicious Latte Macchiato at the touch of a button

The Saeco Incanto has set a new standard in its class. The strikingly refined casing houses high-quality Italian technology, engineered to brew divine coffee, every time. Your coffee dreams have finally been answered.

### **Any coffee for any moment**

- Enjoy 6 beverages at your fingertips
- One-touch Cappuccino and Latte Macchiato with milk carafe
- Adjust the length, 5 aroma strength and 5 grinder settings
- Adjust and store your personal user profile

### **Every coffee crafted to perfection**

- 20,000 cups of finest coffee with durable ceramic grinders
- Perfect milk foam thanks to Latte Perfetto technology
- Premium PianoBlack finishing, shaped to precision
- Hot coffee from the first cup with Thermoblock

### **Attentive and anticipating at your command**

- Featuring AquaClean for up to 5000\* cups without descaling
- Clean milk residues after every use with milk clean function
- Designed to maximize capacities in a compact footprint
- Enjoy a great coffee with Auto-Rinse & guided descaling

**PHILIPS**

Saeco, a Philips brand

 **Saeco**

# Highlights

## 100% ceramic grinders




Our grinders are made of high-tech ceramic: exceptionally hard and precise. Fresh beans are gently ground, without risk of overheating: extracting all the best flavors and aroma, delivering a superior coffee taste for at least 20,000 cups.

## 6 beverages



Enjoy a wide variety of drinks to suit any occasion. Whether you crave for an espresso, a coffee or a milk based recipe, your Super-automatic machine delivers a perfect in-cup result with no hassle and in no time!

## AquaClean filter



# AquaClean

AquaClean is our patented water filter, designed to improve the quality of your coffee

by purifying water. It also prevents scale build-up in the water circuit of your coffee machine: make up to 5000\* cups without descaling by replacing the filter regularly.

## Auto-Rinse & Guided descaling



This espresso machine automatically cleans its coffee circuit with water upon starting up or switching off of the machine, this delivers a great, fresh taste with each cup of coffee. Regular descaling prolongs your espresso machine's life. This machine will prompt when descaling is needed. It will guide you with on-screen messages what you have to do and when.

## Customize your coffees



This Super-Automatic machine offers an abundance of indulgent options to customize your beverage to your taste. You can easily personalize and memorize length, strength and temperature for each drink. Feel free to explore, experiment and dream up any drink!

## High capacity & compact design



Enjoy more room and go longer without refill thanks to the high-capacity bean, water, and waste containers in a super-compact design. This smart, super-automatic machine provides you with maximum convenience and top notch performance thanks to a large capacity water tank, bean and waste container.

## Integrated milk carafe



Enjoy super creamy cappuccino and Latte Macchiato at the perfect temperature, in the easiest way possible. Simply pour milk into the carafe, plug it into the machine, and select your preferred beverage. Whether it's a cappuccino or frothed milk, your drink will be served within seconds, with a splash-free flow at the ideal temperature.

# Specifications

## Customization

- Aroma Strength Settings: 5
- Coffee and Milk Length: Adjustable
- Grinder Settings: 5
- Pre Brew Aroma control: No
- Temperature settings: 3
- User Profiles: 1

## General specifications

- Milk Solution: Integrated Milk Carafe, Quick Milk clean
- User Interface: Basic Display
- Type of carafe: Basic carafe

## Other features

- Auto-Rinse & Guided descaling
- Gusto perfetto
- Main Switch ON / OFF button
- Quick Heat Boiler
- Removable brew group

## Technical specifications

- Capacity milk carafe: 0.5 L

- Capacity waste container: 15 servings
- Capacity water tank: 1.8 L
- Coffee bean capacity: 250 g
- Color & Finishing: PianoBlack
- Cord length: >100 cm
- Country of origin: Romania
- Filter compatibility: AquaClean
- Frequency: 50 Hz
- Max. cup height: 150 mm
- Product dimensions: 221 x 340 x 430 mm
- Voltage: 230 V
- Waste container: Frontal access
- Water tank: Access from the top
- Weight of product: 7.2 kg

## Variety

- Beverages: Cappuccino, Espresso, Espresso Lungo, Hot water, Latte Macchiato, Milk froth
- Coffee Powder Option
- Double Cup
- Milk Double Cup: No