



## Saeco Incanto Super-automatic espresso machine

- 6 Beverages
- Integrated premium milk carafe
- Titanium Stainless Steel
- 5 step adjustable grinder

HD8922/09



Elegant design. Impressive coffee quality.

Delicious Latte Macchiato at the touch of a button

The Saeco Incanto sets a new standard in its class. The refined, stainless steel front houses high-quality Italian technology, engineered to brew divine coffee, every time. Your coffee dreams have finally been answered.

### Advanced technology designed for coffee perfection

- 20,000 cups of finest coffee with durable ceramic grinders
- Enjoy hot coffee in no time with the Quick Heat Boiler
- Delicious hot Cappuccino and Latte Macchiato at one touch
- Fine-tune the coffee's richness with 5 grinder settings

### High comfort is part of the experience

- Up to 5000 cups\* without descaling with AquaClean filter
- Limited edition hand-crafted Titanium stainless steel
- Auto-cleaning cycle removes any hassle
- The fully removable brewing group can be cleaned in no time

### A variety of coffees customized to your taste

- A multitude of specialty coffees at the touch of a button
- Decaffeinated with equal zest with the Powder Option
- The strength selection remembers just how strong you like it

**PHILIPS**

Saeco, a Philips brand

 **Saeco**



# Highlights

## Limited edition

Every minute detail of this machine was designed and crafted to the highest quality. The solid, stainless steel front, vibrant display, and tactile feel of each button are the perfect balance of elegance, intuitiveness and Italian craftsmanship. The Saeco Incanto will grace any modern or traditional kitchen it finds for years to come.

## 100% Ceramic grinders



Our grinders are made of high-tech ceramic: exceptionally hard and precise. Fresh beans are gently ground, without risk of overheating: extracting all the best flavors and aroma, delivering a superior coffee taste for at least 20,000 cups.

## Quick Heat Boiler



When time is of the essence, you can brew perfect espresso and cappuccino without the wait, thanks to the Quick Heat Boiler. The

secret is in its light aluminum and stainless steel body, which can reach hot temperatures, fast.

## Specialty coffees at one touch



From, espresso to Lattemacchiato, there is an assortment of options waiting to satisfy your coffee cravings. Whether it's first thing in the morning or an after dinner treat, there's a taste for any time of the day, right at your fingertips.

## AquaClean filter



Saeco's new and patented innovation, AquaClean water filter, ensures you make the most out of your full automatic coffee machine. By changing the filter at machine request, you will not need to descale your machine for up to 5000 cups\*, while getting the benefit of clear and purified water. As an added benefit, the descaling notification alarm is automatically deactivated once AquaClean is installed in your favourite Saeco coffee machine.

## Powder Option



Sometimes it's nice to have the option of a full-bodied, delicious coffee, without the caffeine kick. Thanks to the Powder Option you can make decaffeinated coffee whenever you please.

## Auto-cleaning



The automatic cleaning cycle makes it easy to look after, and it increases the machine's longevity – giving you more time to enjoy your coffee instead of cleaning up.

## One-touch Cappuccino and Latte

For an irresistible, creamy foam consistency, the integrated milk carafe froths the milk twice, removing bubbles and impurities. At one press of a button, a splash-free flow of velvety foam pours straight into your cup at a comfortable temperature. The perfect complement to a rich, flavorsome coffee.

# Specifications

## Accessories

- Included: Water filter

## Finishing

- Material boiler: Stainless steel (Inox)
- Material drip tray: Stainless steel
- Material of spout: Plastic
- Material water tank: Plastic

## General specifications

- Coffee strength settings: 5
- Suitable for: Whole coffee beans, ground coffee powder
- Cups at the same time: 2
- Customizing per drink: Adjustable coffee strength, Adjustable cup volume, Adjustable temperature
- Grinder settings: 5
- One touch variety: 7
- Temperature settings: 3
- Type of carafe: Premium carafe
- Type of display: LCD
- Coffee drinks: Espresso, Cappuccino, hot water
- Milk Solution: Integrated Milk Carafe, Quick Milk clean

## Service

- 2-year guarantee

## Sustainability

- Power consumption brewing: 1850 W

## Technical specifications

- Brewing time one cup: 45 (espresso) to 100 (long coffee) sec
- Capacity milk carafe: 500 L
- Capacity waste container: 15 servings
- Capacity water tank: 1.8 L
- Frequency: 50 Hz
- Max. cup height: 150 mm
- Voltage: 230 V
- Water boilers: 1
- Coffee bean capacity: 250 g
- Color & Finishing: Stainless Steel Titanium
- Cord length: 100 cm
- Country of origin: Romania
- Product dimensions: 221 x 340 x 430 mm
- Filter compatibility: AquaClean
- Waste container: Frontal access
- Water tank: Access from the top
- Weight of product: 7.2 kg

## Weight and dimensions

- Weight incl. packaging: 7.2 kg