



**Saeco PicoBaristo
Super-automatic
espresso machine**

- 7 Beverages
- Automatic Milk Frother
- Stainless steel
- AquaClean



HD8924/01

The largest variety from a compact machine

Enjoy up to 5000 cups* of coffee without descaling

PicoBaristo is a compact machine which spoils coffee lovers for variety. Via the user interface you can choose from a wide choice of specialties at one touch. And with the AquaClean filter you can enjoy up to 5,000 cups* without descaling

Any coffee for any moment

- Enjoy 7 beverages at your fingertips
- Velvety froth at one touch with the Automatic Milk Frother
- Adjust the length, 5 aroma strength and 10 grinder settings
- Adjust and store your personal user profile

Every coffee crafted to perfection

- 20,000 cups of finest coffee with durable ceramic grinders
- Perfect milk foam thanks to Latte Perfetto technology
- Iconic stainless steel finishing, shaped to precision
- Hot coffee from the first cup with Thermoblock

Attentive and anticipating at your command

- Featuring AquaClean for up to 5000* cups without descaling
- Enhanced control of your machine via the advanced display
- Designed to maximize capacities in a compact footprint
- Enjoy a great coffee with Auto-Rinse & guided descaling

 **Saeco**

PHILIPS

Saeco, a Philips brand



Highlights

7 beverages



Enjoy a wide variety of drinks to suit any occasion. Whether you crave for an espresso, a coffee or a milk based recipe, your Super-automatic machine delivers a perfect in-cup result with no hassle and in no time!

Automatic Milk Frother



Preparing a velvety cappuccino is easy thanks to the Automatic Milk Frother. The milk frother, which baristas also call "cappuccinatore", will draw the milk directly from a carton or jug, froth it automatically and dispensing it into your cup with a constant flow of milk without any splashing.

Customize your coffees



This Super-Automatic machine offers an abundance of indulgent options to customize

your beverage to your taste. You can easily personalize and memorize length, strength and temperature for each drink. Feel free to explore, experiment and dream up any drink!

User Profiles

Store the length of any coffee and milk beverage according to your personal taste. You will be able to drink espresso, coffee and all other beverages always as you prefer, at the touch of a button.

100% ceramic grinders



Our grinders are made of high-tech ceramic: exceptionally hard and precise. Fresh beans are gently ground, without risk of overheating: extracting all the best flavors and aroma, delivering a superior coffee taste for at least 20,000 cups.

Latte Perfetto Technology



Every coffee you prepare will be topped with a silky, milk layer that beckons the taste buds. The milk carafe froths the milk twice, then pours a splash free creamy layer into your cup at just the right temperature. The carafe can also be stored conveniently in the fridge and it is incredibly hygienic.

Stainless steel finishing



Every minute detail of this machine was designed and crafted to the highest quality. The stainless steel finishing, inspired by Italian design and craftsmanship will stand the test of time in any classic or modern kitchen. An elegant vision of pure design, your machine will look as refined as the coffee it makes.

Thermoblock



Say goodbye to lukewarm coffee. Thermoblock ensures a hot coffee and cappuccino for you family from the first cup, in no time. The secret is in its light aluminum and stainless steel body, which can reach hot temperatures, fast.

Specifications

Customization

- Aroma Strength Settings: 5
- Coffee and Milk Length: Adjustable
- Grinder Settings: 10
- Pre Brew Aroma control: No
- Temperature settings: 3
- User Profiles: 1

General specifications

- Milk Solution: Automatic milk frother
- User Interface: Advanced display

Other features

- Auto-Rinse & Guided descaling
- Gusto perfetto
- Main Switch ON / OFF button
- Quick Heat Boiler
- Removable brew group

Technical specifications

- Capacity waste container: 15 servings

- Capacity water tank: 1.8 L
- Coffee bean capacity: 250 g
- Color & Finishing: Stainless Steel
- Cord length: >100 cm
- Country of origin: Romania
- Filter compatibility: AquaClean
- Frequency: 50 Hz
- Max. cup height: 163 mm
- Product dimensions: 221 x 340 x 430 mm
- Voltage: 230 V
- Waste container: Frontal access
- Water tank: Access from the top

Variety

- Beverages: Caffè crema, Espresso, Espresso Double, Espresso Lungo, Hot water, Milk froth, Ristretto
- Coffee Powder Option
- Double Cup
- Milk Double Cup: No