

PHILIPS

Bread maker

Pure Essentials
Collection

Multi-Shape accessory

14menu 1250g

Black



HD9040/90



Enjoy fresh bread in any shape and flavour Bake your favorite shapes with Multi Bread Shaper!

Enjoy fresh warm loafs every morning and also make your own shapes with this unique Philips bread maker accessory. Bake baguettes, buns, rolls, and fun snacks like pretzels and party rolls. Enjoy with your family and show your creativity!

Bread just the way you like it

- 14 pre-set programmes to bake bread, dough and many shapes
- Up to 15 hours delay timer to enjoy fresh bread any time
- "Add" indicator for speciality breads with extra ingredients
- Bake 3 sizes of loaf – including extra large 1.25kg
- 3 browning levels for your preferred crust

Varieties for every occasion

- Multi Bread Shaper accessory to create your own bread shapes

Great results with ease

- Intuitive operation with easy to use buttons for all users
- Handy recipe booklet included
- Measuring cup and spoon included
- Watch bread rise and brown in viewing window

With maximum safety

- Integrated non-slip handles for easy and safe handling

Highlights

Multi Bread Shaper accessory



The Multi bread Shaper is a unique accessory that allows you to bake bread in any shape. It'll bake baguettes, buns or rolls, and even fun snacks like pretzels and party rolls that the whole family will love. It comprises two trays, each with three separators that you can use to create different sizes and shapes for the dough. You can make up to 12 small buns – great when decorated with seeds for dinner with friends or made with cheese for a savory snack – also combine baguettes with rolls or alternatively, leave out the separators and shape the dough however you like. Show your creativity!

14 varieties of programmes



The Philips Breadmaker has 14 pre-set programmes that bake any bread to perfection, from rich and satisfying whole wheat to gluten free, French and sweet varieties. It also makes delicious dough for pasta, pizza, bagels, cookies and pastries – and jams too. Whatever you bake, it's always delicious and easy to do because the pre-sets take care of the temperature and time for the best possible results. There are even special settings for smaller bread shapes and, if you're in a hurry, a set of rapid programmes for baking in double quick time or even in one hour only.

15-hour delay timer

Enjoy the irresistible smell of fresh warm bread every morning – a true treat and the perfect way to start the day! Simply set the delay timer

the night before and the breadmaker will prepare and bake your loaf while you sleep for freshly baked bread to eat the moment you wake up, or whenever you like.

Add ingredients indicator



Bake speciality breads with tasty extras like nuts or dried fruit – it's easy and fun to do. When the "add" indicator comes up, simply add the extra ingredients to the dough, and let the breadmaker do the rest. Add anything you like – nuts, seeds, olives, dried fruit, cheese, onion, bacon, nougat, chocolate and many more for speciality bread with a delicious difference!

Easy to use buttons

The Philips breadmaker's operational buttons are arranged intuitively and in order to set the programs easily. First, select the bread type, then the weight according to the recipe and the browning level (or simply use the browning level pre-set), then start the program. Large friendly icons illustrate clearly what each button does, and a clear LCD screen confirms the options you've selected.

Extra large bread size



Don't worry about wasting bread or running out if you need to feed a few extra people. Use the breadmaker's extra capacity and clear markings to bake medium, large and extra large loaves of 750g, 1kg and 1.25kg.

3 browning levels



You can enjoy your bread just as you like it with three browning levels. Choose a light, medium or dark crust, depending on your preference and on your favorite recipes.

Handy recipe booklet included



Like to try something new sometimes? The handy recipe booklet tells you how to make specialty breads, and has lots of tasty tricks and tips for adding your favourite ingredients to make something special out of any recipe. What's more, it's clear to follow and easy to do, even if you've never used a breadmaker before.

Viewing window

The viewing window allows you to watch the breadmaker at work, kneading, mixing and baking – it's ideal if you want to check the progress and ensure everything's going to plan.

Specifications

General specifications

Hours of delay timer: 15

Add ingredients signal

One-touch operation

Dough program: Pasta, general (pizza, cookie, baguel, etc)

Recipe booklet

Rapid program

Bake only

Jam program

Specialty programs: Bread shaper, Bread shaper sweet

Browning levels: 3

Warming period: 1 hour

Viewing window

No. of paddles: 2

LCD display

Cool wall exterior

Non-slip feet

Cord storage

Bread capacity: 750 gr, 1000 gr, 1.25 Kg

No. of programs: 14

Accessories included

Paddle(s)

Measuring cup

Measuring spoon

Additional utensils: Cutting blade and basting brush

Baking accessory: Multi bread shaper with removable separators

Baking tin: Up to 1.25 kg

Design specifications

Color(s): Black, red & brushed metal

Material

Main body: PC plastic, SS metal, glass

Baking tin: Anodized aluminum with double non-stick coating

Mixing paddle: Die cast with non-stick coating

Baking accessory: Anodized aluminum with non-stick coating

Logistic data

Packaging size: 420x277x301 (LxWxH) mm

Product weight: 7.7 kg

