



## Philips Viva Collection Bread maker

- 14-menu
- 1000 g



HD9046/90

# Wake up to fresh bread every day

Bake any flavour. It's easy and delicious!

You will love the irresistible smell of fresh warm bread every morning! It's very simple...

Add your ingredients at night, set the delay timer for next morning, and let the breadmaker do the rest.

### Bread just the way you like it

- 14 pre-set programs for bread, dough, jam and even yoghurt
- 3 browning levels for your preferred crust
- Bake two sizes of loaf up to large 1kg
- Up to 13-hour delay timer to wake up to freshly baked bread
- 'Add' indicator for specialty breads with extra ingredients

### Great results with ease

- Friendly design which is super silent (< 55 dbA) and compact
- Very comfortable control panel position for all users
- Handy recipe booklet included
- Measuring cup and spoon included
- Large viewing window to let you watch bread rise and brown

### Enjoy your home made yoghurt

- Yoghurt container included

# PHILIPS


# Highlights

## 14 programs for bread and jam




The Philips breadmaker has 14 easy-to-use preset programs that bake any bread to perfection, from rich and satisfying whole wheat to gluten free, French and sweet varieties. It also makes specialty breads such as Borodinsky, Easter bread and delicious dough for pasta, even jams too. Whatever you bake, it's always delicious and easy to do because the pre-sets take care of the temperature and time for the best possible results. If you're in a hurry, you can use rapid program for quicker result, or even super rapid program that just bake in one hour only.

## 3 browning levels



Thanks to the advanced temperature control system, the Philips VIVA breadmaker let you enjoy your bread just as the way you like it, whether light, medium or dark crust, only with a simple push on the control panel.

## 2 bread sizes for selection



Bake just the right amount of bread for your needs. Simply choose the loaf size on the control panel to bake medium (750g) or large (1000g) depending on your needs.

## Up to 13-hour delay timer



Enjoy the irresistible smell of fresh warm bread every morning - a true treat and the perfect way to start the day! Simply set the delay timer the night before and the breadmaker will prepare and bake your loaf while you sleep for freshly baked bread to eat the moment you wake up, or whenever you like.

## 'Add' ingredients indicator



During the mixing stage, the breadmaker will give 'beep' sounds to alert you to add other

special ingredients to your specialty bread if you wish.

## Silent (< 55 dbA) and compact



The breadmaker has a very user friendly design which is super silent (55dbA) when operating, so wake you up with the smell of fresh bread, not by the noise. Its compact design is superb to fit for any modern kitchen.

## Very comfortable control panel



Very comfortable control panel position for all users

## Recipe booklet included

Handy recipe booklet included

## Included with cup and spoon

Measuring cup and spoon included

## Large viewing window

Large viewing window to let you watch bread rise and brown

# Specifications

## Accessories included

- Baking tin: Up to 1 kg
- Measuring cup
- Measuring spoon
- Paddle(s)
- Yoghurt container with lid

## Design specifications

- Color(s): Black

## General specifications

- Add ingredients signal
- Bread capacity: 750gr, 1kg
- Browning levels: 3
- Cool wall exterior
- Dough program: Pasta, general (pizza, cookie, baguette, etc)

- Hours of delay timer: 13
- Jam program
- LCD display
- No. of paddles: 1
- No. of programs: 14
- Non-slip feet
- One-touch operation
- Rapid program
- Recipe booklet
- Warming period: 1 hour
- Yoghurt program

## Material

- Baking tin: Aluminum alloy
- Main body: PP plastic
- Mixing paddle: Aluminum alloy



Issue date 2013-05-30

Version: 5.0.1

© 2013 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)