

# PHILIPS

## Steamer

### Pure Essentials Collection

9 L, 900 W

Digital timer, preset timings

Aroma Infuser, keep warm func.

Plastic/Metal, White

HD9140/00



## Discover fuller flavours

### Add your own taste with the flavour booster

The Flavour Booster provides your food with great aromas of herbs and spices. You can prepare favourite soup, stew, porridge, rice and more in the XL steaming bowl. Press the preset time button and off you go!

#### Discover variety of fuller flavours

- Flavour Booster adds more taste with delicious herbs & spices
- XL steaming bowl for soup, stew, rice and more
- Optimal preset timings for fish, vegetables, rice and more
- Recipe booklet

#### Only a little effort

- Dishwasher-safe parts
- External water inlet
- Digital timer
- Keep Warm function keeps food ready for serving

#### Smart features

- Descale indicator and water refill indicator
- Cord storage
- Removable 500 ml drip tray is easy to pour from and clean
- Stackable steaming tiers


# Highlights

## Flavour Booster



The unique Flavour Booster of the Philips steamer adds delicious aroma of herbs and spices, bringing even more taste to steaming. Simply pop your favourite herbs and spices into the booster, and let steam do the rest. The heat from the steam releases delicate aromas from the herbs and spices, which thoroughly infuse the food with their mouth-watering flavours.

## Optimal preset timings



Steaming is a delicate art, which is why the Philips Steamer has a wide range of preset timings that automatically shut off the steam once the ideal steaming time is reached. That will help you to cook a huge variety of foods – including rice, eggs, vegetables, chicken and fish – achieving perfect results that retain all the flavour and vitamins.

## XL steaming bowl



With the XL steaming bowl you can prepare more varied tasty meals for your family. XL steaming bowl for soup, stew, rice and more.

## Dishwasher-safe parts



Dishwasher-safe parts make cleaning easy.

## Stackable steaming tiers



Stackable steaming tiers use less space for storing.

## External water inlet



External water inlet for refilling reservoir during use.

# Specifications

## Design specifications

**Material:** Plastic with stainless steel parts  
**Color(s):** White, metal and red

## Accessories included

XL steaming bowl: 2.5 L  
Egg rack

## General specifications

Non-slip feet  
Power-on light  
Cool-touch handgrips  
Water level indicator  
Overheat and dry boil protection  
Number of tiers: 3 pcs

## Weight and dimensions

**Weight appliance:** 2.3 kg  
**Product dimensions (W x H x D):** 360 x 450 x 227 mm

## Technical specifications

**Power:** 900 W  
**Voltage:** 220–240 V  
**Frequency:** 50/60 Hz  
**Cord length:** 100 cm  
**Capacity (max):** 2.5 / 2.6 / 3.5 L  
**Capacity water tank:** 1.1 L

