

PHILIPS

Kettle

Avance Collection


1.7 liter

2200 W

Brushed metal



HD9326/20



Great tasting hot drinks

Temperature setting for your favorite drinks

Looking for the optimal taste for your drink? To get the maximum flavor, every hot drink should be made at an ideal temperature. By choosing the right temperature button on your kettle, you can now enjoy the optimal taste of your hot drink.

Great tasting hot drinks

- 4 pre-set buttons for selection of your preferred hot drink
- Keep warm function keeps the water at your set temperature

Fast boiling and easy cleaning

- Robust metal kettle with brushed stainless steel body
- Flat heating element for fast boiling and easy cleaning
- Micro-mesh filter for a clean cup of water

Easy to experience

- Easy lid and spout filling
- Spring lid with large opening for easy filling and cleaning
- Power cord winder for easy storage
- Cordless 360° pirouette base for easy lifting and placing
- Easy to read water level indicator

Safe to use

- Multi safety system

Highlights

4 pre-set hot drink buttons



The pre-set temperature settings of 80, 90, 95 and 100°C will ensure that the basic ingredient for your tea, instant coffee, soup or noodles is at the temperature you like.

Keep warm function



You do not need to re-boil your water continuously anymore. The keep warm function ensures that the water is kept warm at the right temperature for the selected preset.

Robust metal kettle



Robust metal kettle with brushed stainless steel body is made to have a long lifetime.

Flat heating element

The stainless steel concealed element ensures fast boiling and easy cleaning.

Easy lid and spout filling



The kettle can be filled via the spout or by opening the hinged lid.

Spring lid



Spring lid with large opening for easy filling and cleaning, also avoiding steam contact.

Power cord winder



The cord can be wrapped around the base, so that the kettle is easy to place in your kitchen.

Cordless 360° pirouette base



Cordless 360° pirouette base for easy lifting and placing.

Water level indicator



Easy to read water level indicator

Multi safety system

Multi safety system against boil-dry, with auto switch off when ready

Micro-mesh filter



The removable micro-mesh filter on the spout restrains all scale particles with size > 200 micron and ensures that the water you put into your cup is clean.



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO₂ emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Country of origin

Made in: China

General specifications

Product features: 360 degrees base, Automatic shut-off, Boil-dry protection, Cord storage, Flat heating element, Non-slip feet, On/off switch, Temperature control

Service

2-year worldwide guarantee

Technical specifications

Capacity jar: 1.7 L
Frequency: 50-60 Hz
Power: 1850-2200 W
Voltage: 220-240 V

Design

Color of control panel: Brushed Metal

Finishing

Material filter: Nylon
Material heating element: Stainless steel
Material of main body: Stainless steel
Material switch: PP

