

PHILIPS

Kettle

Daily Collection

1.0 L, 2000W

plastic

Star white & Caribbean blue

Kettle



HD9344/12



Stylish design, compact size

See-through design helps you boil what you need

Your Philips kettle is designed to be fully protected and sealed. It is completely free from steam or water dripping.

Easy to experience

- Compact design to boil only the water you need
- Translucent water level indicator
- Cordless 360° pirouette base for easy lifting and placing
- Power cord winder for easy storage

Easy to clean

- Removable lid and wide opening for easy cleaning
- Micro-mesh filter for a clear cup of water
- Flat heating elements for fast boiling and easy cleaning

Safe to use

- Steam leak-proof design for lid, handle and switch
- Multiple safety system against boil-dry

Highlights

Compact design



Enables you to boil the amount of water you need in a quicker way, whilst occupying less space from your countertop.

Translucent body

The water level is easy to read from every angle thanks to the translucent body. The stylish stripes smartly indicate the exact water amount, as every stripe represents an additional cup (250ml) of water.

Cordless 360° pirouette base



Cordless 360° pirouette base for easy lifting and placing.

Power cord winder



The cord can be wrapped around the base, so that the kettle is easy to place in your kitchen.

Removable lid




Your hand can fit easily to clean the kettle thanks to the fully removable lid and wide opening.

Micro-mesh filter



The removable fine micro-mesh filter on the spout restrains all scale particles with size > 180 micron and ensures that the water you put into your cup is clean.

Flat heating element



The stainless steel concealed element ensures fast boiling and easy cleaning.

Steam leak-proof design



The lid, handle and switch are completely steam proof for maximum safety.

Multiple safety system



The kettle shuts off automatically when the water is ready, when it is lifted from the base or when there is too little water.

Specifications

Country of origin

Made in: China

General specifications

Product features: 360 degrees base, Automatic shut-off, Boil-dry protection, Cord storage, Flat heating element, Non-slip feet, On/off switch, Lid and spout filling

Service

2-year worldwide guarantee

Technical specifications

Capacity jar: 1.0 L
Cord length: 0.75 m
Frequency: 50/60 Hz
Power: 2000 W
Voltage: 220-240 V

Weight and dimensions

Micromesh filter: 200 µm

Design

Color: Star White and Caribbean Blue

Finishing

Material heating element: Stainless steel
Material of main body: PP plastic
Material switch: PP plastic

