

PHILIPS

Glass kettle

Avance Collection

1.7 liter

2200 W

Temperature control

HD9382/20



Extra robust, long-lasting SCHOTT DURAN glass

Temperature settings for your favourite drinks

Looking for the optimal taste for your drink? To get the maximum flavour, every hot drink should be made at an ideal temperature. By choosing the right temperature icon on your kettle, you can now enjoy the optimal taste of your hot drink.

Great tasting hot drinks

- 4 pre-set buttons for selection of your preferred hot drink
- Keep warm function keeps the water at your set temperature

Fast boiling and easy cleaning

- Flat heating element for fast boiling and easy cleaning
- Anti-calc filter for a clean cup of water

Easy to experience

- Cordless 360° pirouette base for easy lifting and placing
- Multi safety system
- Easy to read water level indicators on both sides
- Hinge lid with release button for easy filling and cleaning
- One cup indicator to boil only the water you need

Robust and long-lasting

- SCHOTT DURAN® glass made in Germany is perfect for boiling



asimpleswitch.com

Highlights

4 pre-set hot drink buttons



The pre-set temperature settings of 80, 90, 95 and 100°C will ensure that the basic ingredient for your tea, instant coffee, soup or noodles is at the temperature you like.

Keep warm function



You do not need to re-boil the water continuously anymore. The keep warm function ensures that the water is kept warm at the right temperature for the selected preset.

Flat heating element

The stainless steel concealed element ensures fast boiling and easy cleaning.

Cordless 360° pirouette base



Cordless 360° pirouette base for easy lifting and placing.

Multi safety system


Multi safety system against boil-dry, with auto switch off when ready or when lifted from the base.

SCHOTT DURAN® glass



The kettle body is made of special glass by SCHOTT DURAN® in Germany which is extra robust, long-lasting and best for high temperature application like boiling.

Easy water level indicator



Easy to read water level indicators on both sides

Hinge lid with release button



Hinged lid with release button for easy filling and cleaning, also avoiding steam contact.

One cup indicator



Enabling consumers to boil the amount of water they need, and therefore saving up energy and water, contributing to a better environment.

Anti-calc filter



Anti-calc filter for a clean cup of water and a cleaner kettle.



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Design specifications

Color(s): Stainless Metal / Black

Heating element: Stainless steel

Material housing: Stainless metal/glass

Material switch: Polypropylene (PP)

General specifications

Cordless

Ergonomic grip

Wide opening lid

Cord storage

Automatic shut-off

Boil-dry protection

360 degrees base

Flat heating element

Non slip feet

Accessories

Filter: Single action filter

Technical specifications

Capacity: 1.7 L

Power: 2200 W

Cord length: 0.75 m

Frequency: 50/60 Hz

Voltage: 220-240 V

Dimensions

Product dimensions (WxDxH): 20 x 27 x 23 cm

Packaging dimensions (WxDxH): 23,6 x 35,6 x 23,6 cm

Service

2-year worldwide guarantee

