

PHILIPS

Kettle

Avance Collection

1.7 L 2400 W

Digital temp control

Ink black

Spring lid



HD9384/20



Great tasting hot drinks

With optimal temperature settings for your drink

Looking for the optimal taste for your drink? To get the maximum flavour, every hot drink should be made at an ideal temperature. By choosing the right temperature icon on your kettle, you can now enjoy the optimal taste of your hot drink.

Great tasting hot drinks

- Keep warm function keeps the water at your set temperature
- 5 pre-set buttons for selection of your preferred hot drink

Fast boiling and easy cleaning

- Flat heating element for fast boiling and easy cleaning
- Spout filter for a cleaner cup and kettle
- One cup indicator to boil only the water you need

Easy to experience

- Easy lid and spout filling
- Cordless 360° pirouette base

Safe to use

- Multi safety system

Highlights

Keep warm function



You do not need to re-boil your water continuously anymore. The keep warm function ensures that the water is kept warm at the right temperature for the selected preset.

Easy lid and spout filling



The kettle can be filled via the spout or by opening the lid.

Flat heating element



The stainless steel concealed element ensures fast boiling and easy cleaning.

Cordless 360° pirouette base



Cordless 360° pirouette base for easy lifting and placing.

Multi safety system



Multi safety system against boil-dry, with auto switch off when ready

Spout filter



The fine micro-mesh filter on the spout ensures that the water you pour into your cup is clean and no calc particles end up in your drink.

Specifications

Accessories

Included: Spout filter

General specifications

Product features: 360 degrees base, Automatic shut-off, Boil-dry protection, Cord storage, Flat heating element, Ergonomic grip, Lid and spout filling, Wide opening lid

Service

2-year worldwide guarantee

Technical specifications

Capacity: 1.7 L

Power: 2400 W

Weight and dimensions

Dimensions of packaging (LxWxH): 236 x 356 x 236 mm

Dimensions of product (LxWxH): 200 x 270 x 230 mm

Design

Color: Ink Black

Finishing

Material heating element: Stainless steel

