

PHILIPS

Straightener

ProCare

Sonic



HP8349/00



Maximum protection, ultimate shine

Straighten without overheating

Ultimate hair care. The Philips ProCare Sonic straightener protects the hair from overheating, due to its newly developed Triple-Care™ plates with constant temperature, EHD technology™ and Sonic technology™

Beautifully styled hair

- Ceramic plates for smooth gliding and shiny hair
- Great results in less time with gentle Sonic vibrations
- More care with ion conditioning for shiny, frizz-free hair

Less hair damage

- Healthy hair without hotspots with Even Heat Distribution
- Caring and efficient straightening with constant temperature

Ease of use

- Automatic shut-off after 60 min
- Closing lock to close the handle for easy and safe storage
- Included: heat resistant mat
- Fast heat up time, ready to use in 15 seconds
- No more accidental change of settings with key-lock function
- Universal voltage

Highlights

Safe usage

Some hair straighteners and curling irons have been equipped with an automatic shut-off feature. This feature has been designed to provide peace of mind. If left on, the appliance will automatically switch off after 60 min.

Ceramic plates

Ceramic is microscopically smooth and durable by nature and it is one of the best materials for straightening plates. The plates glide effortlessly through your hair, giving you perfect shiny hair.

Constant temperature



This straightener keeps a more constant temperature. Thanks to its high-performance heater it allows you to straighten your hair at a more caring temperature while getting the exact style you want!

Even Heat Distribution

Advanced Philips EHD+ technology means that your styler will always distribute the heat very evenly - even at high temperatures, and prevents damaging hot spots. This gives added protection and thus helps to keep your hair healthy and shiny.

Handle closing lock

The straightener has a closing lock mechanism. Located at the base of the straightener, this locks plates, making storage quick and easy and helping to protect the straightener from accidental damage.

Heat resistant mat

Included: heat resistant mat

Instant heat up




The straightener has a fast heat up time, being ready to use in 15 seconds

Auto key-lock function

You are always in control. No more accidental switching on/off of the styler or temperature change with the Key-lock function. To unlock, press the button for 3 seconds.

Gentle Sonic vibrations



Great results in less time with gentle Sonic vibrations

Universal voltage



Worldwide voltage for getting the perfect travel companion

Ionic Care



Give your hair an instant care with ionic conditioning. Charged negative ions eliminate static, condition the hair and smooth down the hair cuticles to intensify the hair's shine and glossiness. The result is hair that is beautifully shiny, smooth and frizz-free.

Specifications

Technical specifications

Voltage: 110-240 V

Heating time: 15s

Cord length: 2 m

Color/finishing: Purple black

Heater type: High-performance

Maximum temperature: 199 °C

Features

Ready for use indicator

Swivel cord

Ceramic coating

Ion conditioning

Hair type

End result: Straight

Hair length: Long, Medium, Short

Hair thickness: Medium, Thick, Thin

Service

2-year worldwide guarantee

