

PHILIPS

Jamie Oliver
HomeCooker

1500 W

Stirrer

Steaming tier



HR1040/90



Gentle, constant stirring for tastier cooking

Hands-free and unattended — lets you walk away

The Philips Jamie Oliver HomeCooker with AutoStir technology offers gentle, constant stirring for effortless cooking of both one-pot meals and delicious side dishes. Thanks to the stirring, you can enjoy hands-free cooking and walk away.

Convenient unattended cooking

- AutoStir technology
- Countdown timer with beep
- Easy-to-use timer for 0 – 99-minute settings
- Dishwasher-safe parts for easy cleaning

Cook tastier meals

- 40 – 250°C temperature range
- Includes exclusive HomeCooker recipes by Jamie Oliver
- Stirs itself and is happy unattended, so you can walk away

Cook a wide range of meals

- Cook both one-pot meals and delicious sides
- Also suitable for quicker weekday meals
- Includes steaming tier for more versatility



asimpleswitch.com

Highlights

AutoStir technology



Gentle, constant stirring thanks to AutoStir technology not only ensures that your ingredients brown evenly, but also that the flavours of your ingredients are released, making your dishes tasty.

Beeps to remind you

When the countdown timer on your HomeCooker reaches zero, meaning your attention is needed again, clear beeps call you back from your away time.

QuickSet timer 0 - 99 minutes




With the easy-to-use QuickSet timer, you can set the HomeCooker cooking time and walk away. When your attention is needed, a beep will call you back for the next step.

Dishwasher-safe parts




To optimise the time spent in your kitchen, you can safely put the pan, lid, stirrer and steaming tier in your dishwasher.

From warm to hot



In the HomeCooker, thanks to the wide temperature range of 40 - 250°C, you can melt, simmer, boil, steam and fry. Therefore, you can effortlessly prepare delicious one-pot dishes like risottos, stews, curries and sauces or side dishes like caramelised onions, chutneys, jams and more.

Recipes by Jamie Oliver



Preparing delicious meals in the HomeCooker is easy using the exclusively created Jamie Oliver recipes. Visit <http://www.philips.com/homecooker> for more recipes and inspiration.

Tastier cooking



Gentle, constant stirring thanks to AutoStir technology not only ensures that your ingredients brown evenly, but also that the flavours of your ingredients are released, making your dishes tasty.

Surprisingly versatile



The HomeCooker not only helps in the effortless preparation of one-pot meals like risottos, curries and stews - it also creates great-tasting chocolate fondue, jams and side dishes like chutneys. With the steaming tier you can create even more healthy meals like steamed vegetables, dumplings and fish.

Hands-free / Unattended



Especially on busy weekdays, most of us would like to spend less time in the kitchen. Thanks to the HomeCooker and its gentle, constant stirring, it is possible to cook even while you focus your time and attention on other things. Imagine setting up the HomeCooker with the ingredients for a stroganoff, setting the timer for 30 minutes and being able to walk your dog, spend time with your family or even take a relaxing bath...



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas — Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Accessories included

Steaming tier

Design and finishing

Materials: Stainless steel, plastic

Colour: Black

General specifications

Hot plate indicator light

Cord storage

Non-slip feet

99 minute timer

40-250-degree temperature

Stirrer on/off switch

Ready signal

On/off switch

Automatic shut-off

Lid with steaming hole

Removable heat protection ring

Technical specifications

Power: 1500 W

Voltage: 220-240 V

Frequency: 50/60 Hz

Cord length: 1.0 m

Heating capacity: 3 l

Weight and dimensions

Weight of appliances: ~5280 g

Product dimensions (W x H x D): 324 x 345 x 359

Box dimensions (W x H x D): 385 x 260 x 397

