

PHILIPS

Mixer

Avance Collection

750 W

Infinite speed + turbo

Stainless steel beaters

3.4 L rotating bowl



HR1594/00



Easy from sponge cake to hard dough

True versatilities with accessories

Philips' unique Fleximix reaches all corners and powerful 750W motor ensures supersmooth lump free result. Infinite speed setting gives maximum control over mixing, while dough hooks and the self-driven metal bowl offer real versatility.

Supersmooth, lump free result

- FlexiMix function enables the beaters to reach all corners

Perfect dough and desserts in minutes

- Powerful 750 W motor
- Maximum control over mixing
- Maximum power to your mixing

Handle versatility to perfection

- True versatilities with accessories
- Beaters and dough hooks included
- Dishwasher safe accessories

Simplicity in experience

- For effortless use



asimpleswitch.com

Highlights

Assorted accessories

3.4 L

Assortment of accessories including 3.4L stainless steel mixing bowl to confidently handle a large variety of ingredients for all your favourite recipes

Beaters and dough hooks



A pair of stainless steel beaters and dough hooks for all your recipes to whip/mix and knead to perfection.

FlexiMix function



The unique Fleximix function of the Philips mixer gives freedom to user to move the beaters up and down into all corners of the bowl easily.

Powerful motor

750W

A powerful and silent motor to beat/whip and knead to perfection.

Infinite speed



Varies speed to give you maximum control over your mixing.

Self-driven bowl



Self-driven bowl to effortlessly whip/mix and knead your dough to perfection

Turbo



Turbo speed to whip/mix and knead to perfection

Dishwasher safe



All accessories are dishwasher safe to easily help you keep your versatile product clean



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Accessories included

Stainless steel dough hooks
Stainless steel strip beaters
3.4L stainless steel bowl
Spatula

Design specifications

Color(s): White/black

General specifications

Turbo function
FlexiMix system

Technical specifications

Power: 750 W
Speeds: Varies

Service

2-year guarantee

