

PHILIPS

Hand blender

Viva Collection

650 W, plastic bar

Double action knife

1,7 L Beaker, XL chopper, whisk

16 speeds +turbo



HR1613/01



Enjoy homemade food and drinks any day

Easy blending, chopping, and whisking at any speed

The Philips hand blender combines 650 Watt power with a double-action blade and multiple speed settings, giving a wonderfully smooth result in seconds. Preparing healthy and delicious homemade food has never been so easy!

A smooth result in seconds

- Double action blade that cuts horizontally and vertically
- Select the optimal speed for all type of ingredients
- Extra powerful turbo button for the toughest ingredients
- Powerful 650 W motor

Easy processing and storing

- Soft touch grip and buttons
- 1.7L oval beaker for preparing food or storing the appliance
- Whisk accessory for whipping cream and mayonnaise
- Chopper accessory

No splashing while you blend

- Anti-splash blade guard with special wave shape

Quick and easy cleaning

- Detachable plastic bar

Highlights

16-speeds and turbo



With 16 speed settings you can select the optimal speed for all type of ingredients creating the preferred consistency or smoothest blending results.

Turbo button

For the toughest ingredients.

Double-action blade



Double action blade that cuts horizontally and vertically

Anti-splash blade guard



The special wave shape in the bottom part of the handblender blending bar guarantees no splashes or mess while you blend.

1.7 L oval beaker



1.7L oval beaker for preparing food or storing the appliance

Chopper accessory

Chopper accessory to chop onion, cheese and more.

Whisk accessory for whipping



Whisk accessory for whipping cream and mayonnaise

Detachable plastic bar

Detachable plastic bar

Soft touch grip and buttons

The soft touch grip and buttons provide comfort when using the product.

Powerful 650 W motor

650 W

Powerful 650 W motor

Specifications

Design specifications

Color(s): White and lavender

Material bar: Plastic

Material blade: Stainless steel

Material housing: PP and rubber

Material jar: SAN

General specifications

Turbo function

Detachable shaft: With 2 buttons

Speed setting: 16

Accessories

Chopper: Compact chopper

Whisk

Beaker

Technical specifications

Capacity beaker: 1.7 l

Frequency: 50/60 Hz

Voltage: 220-240 V

Wattage: 650 W

Cord length: 1.3 m

