

PHILIPS

Blender

Avance Collection

800 W

2 L stainless steel jar

with spatula

ProBlend 6

HR2097/00



Best blending, leaves no bits

ProBlend 6 technology for up to 50% finer result*

The Philips blender with ProBlend 6 star blade with 800 W motor, which can handle just about anything - from fruit and vegetables to ice. Its multi-speed function will blend, crush & cut for perfectly smooth blending & any consistency you want

Make perfect smoothies and crush ice instantly

- ProBlend 6 star blade for blending and cutting effectively
- Unique off-center jar design to mix ingredients efficiently
- Powerful 800 W motor
- Max 2L (with food 1.5L) high quality stainless steel jar
- Viewing window

Choose the exact speed you need

- Variable speed control with illuminated display
- Programmed ice crushing function
- One touch pulse and smoothie button

Ease of use

- Spatula for mixing ingredients easily

Easy to clean


- Easy cleaning with detachable blade
- All parts dishwasher safe, except for main unit



asimpleswitch.com

Highlights

ProBlend 6 star blade



Philips blender with innovative ProBlend 6 technology for blending fruits, cutting vegetables and crushing ice with the most effective way.

Unique jar



blade positioned off-center in the jar will create turbulence and mixing ingredients most effective way.

800 W motor



This Philips blender has a strong 800 W motor for blending, mixing and crushing effectively.

2L stainless steel jar



The 2L jar is made of high quality stainless steel which is scratch proof, and allows to process hot ingredients.

Variable speed control with illuminated display



Set the blender to the speed you want with this unique control knob.

Programmed ice crush function



Motor will operate pre-programmed sequence to crush ice easily with the touch of a button

Pulse and smoothie button



Pulse button to control the operation whatever you want and smoothie button for making the best tasting smoothie by pressing once.

Spatula



The handy spatula of the Philips blender ensures a safe stirring while blending the ingredients.

Detachable blade unit



Easy cleaning with detachable blade



IF DESIGN AWARD

IF award-winning products and projects, concepts and more, selected by the top names in design. Each year, iF International Forum Design GmbH organizes one of the world's most celebrated and valued design competitions: the iF DESIGN AWARD. Recognized as a symbol of design excellence around the world, the iF DESIGN AWARD welcomes over 5,000 submissions from 70 countries every year.



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

General specifications

Number of speed settings: 4

Product features: Cord storage, Non-slip feet

Technical specifications

Power: 800 W

Voltage: 220-240 V

Frequency: 50/60 Hz

Capacity jar: 2 L

Cord length: 1 m

Effective capacity: 1.5 L

Design

Color: Anthracite

Finishing

Material blade: Stainless steel

Material jar: Stainless steel

Material of main body: Aluminium

