

PHILIPS

Innergizer High
Speed Blender

Avance Collection

2000W

45000 RPM

HR3868/00



Unlock More Nutrients

Release 97% of nutrients from fruit and vegetables

High Speed Blender with ProBlend Extreme nutrient release technology releases 97% of nutrients from fruits and vegetables*

Unlocks nutrient from cells to be absorbed by body

- Powerful 2000 W power and 45000 RPM
- ProBlend Extreme Technology

Smooth blending for homemade smoothies easily

- Nutritionist selected 40 smoothies recipes to fit your needs
- 2L Tritan Jar for everyday nutrients and fiber intake
- Digital UI Screen with 5 pre-programmed modes
- Manual mode with variable speed options

Ease of Use & Quality Guaranteed

- Comes with 2 years guarantee
- Easy to clean
- Dishwasher safe except for the main unit

Quiet operating function

- Noise comfort dome to reduce blending noise



asimpleswitch.com

Highlights

Powerful blending




Powerful blending with 2000 W and 45000 RPM

ProBlend Extreme Technology

'ProBlend Extreme' nutrient release technology unlocks nutrients from cells to be absorbed by the body.

Health tips and recipes



Nutritionist selected 40 smoothies recipes to fit your needs.

2L Tritan Jar



2L Tritan Jar for everyday nutrients and fiber intake

Digital UI Screen



Digital UI Screen with 5 pre-programmed modes and manual mode with variable speed options.

Manual mode



Manual mode with various speed options

2 years guarantee



Comes with 2 years guarantee

Quieter operating system

Noise comfort dome to reduce blending noise for convenience use especially in the morning.

Easy to clean



Easy to clean

Dishwasher safe



Dishwasher safe except for the main unit



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Accessories

Included: Tamper

Country of origin

Made in: China

General specifications

Number of speed settings: 10

Prefix programs: 5

Product features: Automatic shut-off, Cord storage, Dishwasher safe, LED display, On/off switch, Pulse, Variable speed, Removable lid

Service

2-year worldwide guarantee

Sustainability

Packaging: > 90% recycled materials

User manual: 100% recycled paper

Technical specifications

Cord length: 1.2 m

Power: 2000 W

RPM blender (max): 45000 rpm

Voltage: 200-230 V

Effective capacity: 2.0 L

Finishing

Material accessories: Plastic ABS

Material jar: Tritan

Material of main body: Stainless steel

