



Philips Immersive Sound  
Home theatre

3D Angled Speakers

HDMI 1080p

Immersive Sound

HTS5550



## Obsessed with sound

True cinematic experience with sound evenly spread

Maximise your home cinema sound experience with dynamic 3 Directional Angled Speakers! Play your favourite entertainment content on the innovative Philips 5000 series home theatre system

### Great listening experience

- 3D Angled Speakers disperse sound evenly around the room
- 1200 W RMS power delivers great sound for movies and music
- DTS, Dolby Digital and Pro Logic II surround sound
- DoubleBASS technology for fuller and deeper bass

### Designed to enhance your living space

- Sleek high gloss finishing with unique touch controls


### Connect and enjoy all your entertainment

- Plays DVD, VCD, CD and USB devices
- Wireless rear audio ready for fewer wires across your room

**PHILIPS**  
sense and simplicity

# Highlights

## 3D Angled speakers




3D Angled Speakers feature angled drivers to deliver sound not only towards the front but also to the sides, creating a wider sweet spot so you can enjoy more immersive and cinematic surround sound.

## 1200 W RMS power




1200 W RMS power delivers great sound for movies and music

## DoubleBASS technology



DoubleBASS ensures you hear even the deepest bass tones from compact-sized subwoofers. It captures low frequencies and recreates them in the audible range of the subwoofer - delivering sound with more boom and panache, and ensuring you get a full, uncompromised listening experience.

## DTS, DolbyDigital, ProLogic II



A built-in DTS and Dolby Digital decoder eliminates the need for an external decoder by processing all six channels of audio information to provide a surround sound experience and an astoundingly natural sense of ambience and

dynamic realism. Dolby Pro Logic II provides five channels of surround processing from any stereo source.

## Plays it all



Play virtually any disc and any media devices you want - whether they are DVDs, VCDs, CDs or USB devices. Experience the unbeatable convenience of great playability, and the luxury of sharing media files on your TV or home theatre system.

## Sleek high gloss finishing



Sleek high gloss finishing with unique touch controls

# Specifications

## Accessories

- Compatible accessories: RWSS5510 Wireless Rear Audio, STS1300 Floor stand
- Included accessories: Batteries for remote control, FM antenna, HDMI cable, Power cord, Quick start guide, Remote Control, Stand Screw x 4, User Manual, World Wide Warranty leaflet

## Audio Playback

- Compression format: MP3, WMA
- MP3 bit rates: 32 - 320 kbps

## Still Picture Playback

- Picture Enhancement: Rotate, Slideshow with music playback, Zoom
- Compression format: JPEG, JPEG HD

## Video Playback

- Compression formats: DivX Ultra, MPEG1, MPEG2, MPEG4, XviD, WMV SD
- Video disc playback system: NTSC, PAL

## Optical Playback Media

- Playable Discs: CD, CDDA, CD-R/CD-RW, DVD, DVD +R/+RW, DVD -R/-RW, SVCD, VCD

## File Format

- Audio: mp3, wma
- Picture: JPEG, JPG
- Video: asf, avi, DivX, mpeg, mpg, wmv

## Connectivity

- Front/Side connections: MP3 Link, USB
- Rear Connections: AUX IN 1, Composite video (CVBS) output, Digital coaxial in, Easy-Fit Speaker Connectors, FM Antenna Socket, Wireless Rear Audio, Scart, HDMI 1.3 output

## Convenience

- EasyLink: One touch play, One touch standby, Remote Control-Passthrough

## Dimensions

- Main Unit (W x H x D): 435 x 58 x 358 mm
- Main Unit Weight: 3.56 kg
- Centre Speaker (W x H x D): 280 x 95 x 92 mm
- Centre Speaker Weight: 1.40 kg
- Centre Speaker cable length: 2 m
- Front Tallboy Speaker (W x H x D): 260 x 1101 x 260 mm
- Front Speaker Weight: 3.77 kg

- Front Speaker cable length: 4 m
- Rear Tallboy Speaker (W x H x D): 260 x 1101 x 260 mm
- Rear Speaker Weight: 3.77 kg
- Rear Speaker cable length: 10 m
- Subwoofer (W x H x D): 196 x 395 x 342 mm
- Subwoofer Weight: 5.25 kg
- Subwoofer cable length: 4 m
- Packaging (W x H x D): 400 x 697 x 1200 mm
- Weight incl. Packaging: 32.97 kg

## Loudspeakers

- Loudspeaker types: 1 x Centre speaker, 4 x Tallboy speakers
- Centre speaker drivers: 2 x 3" full range woofers
- Centre speaker freq. range: 150–20k Hz
- Centre speaker impedance: 3 ohm
- Drivers per Tallboy speaker: 2 x 3" Full range woofers
- Tallboy speaker freq range: 150–20k Hz
- Tallboy speaker impedance: 4 ohm
- Subwoofer type: Passive
- Subwoofer driver: 1 x 6.5" woofer
- Subwoofer freq range: 20–150 Hz
- Subwoofer impedance: 3 ohm

## Picture/Display

- Picture enhancement: High Def (720p, 1080i, 1080p), Progressive scan, Video upscaling

## Power

- Power consumption: 150 W
- Power supply: 220-240 V, 50 Hz
- Standby power consumption: < 0.9 W

## Sound

- Equalizer settings: Action, Classic, Concert, Drama, Jazz, Rock, Sports
- Sound Enhancement: Dialogue Enhancer, Dolby Digital Prologic II, DoubleBass, FullSound, Night Mode
- Sound System: Dolby Digital 5.1, DTS 96/24, DTS Digital Surround, Stereo
- Frequency response: 20-20 k Hz
- Signal to noise ratio: > 65 dB
- Total Power RMS @ 30% THD: 1200 W

## Tuner/Reception/Transmission

- RDS: Station Name
- Tuner Bands: FM
- Number of Pre-set Channels: 40



Issue date 2012-05-15

Version: 13.4.10

12 NC: 8670 000 60047  
EAN: 87 12581 52609 2

© 2012 Koninklijke Philips Electronics N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips  
Electronics N.V. or their respective owners.

[www.philips.com](http://www.philips.com)