



1

FY2401

FY2402(HU4816)

In dry conditions moisture from the humidifier will be absorbed by walls, furniture, and other items in your room. Ventilation of dry outside air will also increase the time it takes to reach the target humidity. To optimize humidification performance, it's recommended to close doors and windows during use.

在干燥条件下，加湿器产生的水分会被墙壁、家具和房间内的其他物品吸收。外部干燥空气的流通也会增加达到目标湿度所需的时间。要优化加湿性能，建议在使用过程中关闭门窗。

1

0.5h

1. Fill the water tank with tap water. 2. Do not use hot water (>40°C). 3. Do not use filtered water.

2

1. Fill the water tank to the MAX level. 2. Do not use hot water (>40°C).

2 HU4803/HU4813

1. Press the power button to turn on the humidifier. 2. Turn the dial to the desired mode and settings.

Auto mode 自动模式
Sleep mode 睡眠模式
Fan speed 1 风扇转速 1
Fan speed 2 风扇转速 2

Set the timer 设置定时器





Set the humidity

If no preset humidity level is selected, the humidifier will stop working when the humidity level reaches 50RH% in the auto mode and 70RH% in other modes.

设置湿度


如果未选择预设的湿度，则湿度在自动模式下达到 50RH% 时，在其他模式下达到 70RH% 时，加湿器将停止工作。





Recommend to clean the humidification filter every week to keep hygienic. Please soak the humidification filter with mid or acid cleanser (24g citric acid with 4L water) for 1 hour.

建议每周清洁加湿滤网，保持卫生。请使用中性或酸性清洁剂（24克柠檬酸兑4升水）浸泡加湿滤网1小时。



Replace the humidification filter every 6 months.
请每6个月更换一次加湿滤网。

产品：飞利浦空气加湿器
型号：HU4801
额定电压：220V~
额定频率：50Hz
额定输入功率：14W
生产日期：请见产品本体
产地：中国福建厦门

飞利浦家电（中国）投资有限公司
上海市静安区灵石路728弄20号201室
全国顾客服务热线：4008 800 008
本产品根据国标 GB4706.1-2005, GB4706.48-2009 制造

产品：飞利浦空气加湿器
型号：HU4802
额定电压：220V~
额定频率：50Hz
额定输入功率：14W
生产日期：请见产品本体
产地：中国福建厦门

飞利浦家电（中国）投资有限公司
上海市静安区灵石路728弄20号201室
全国顾客服务热线：4008 800 008
本产品根据国标 GB4706.1-2005, GB4706.48-2009 制造

产品：飞利浦空气加湿器
型号：HU4803
额定电压：220V~
额定频率：50Hz
额定输入功率：18W
生产日期：请见产品本体
产地：中国江苏苏州

飞利浦家电（中国）投资有限公司
上海市静安区灵石路728弄20号201室
全国顾客服务热线：4008 800 008
本产品根据国标 GB4706.1-2005, GB4706.48-2009 制造

产品：飞利浦空气加湿器
型号：HU4811
额定电压：220V~
额定频率：50Hz
额定输入功率：18W
生产日期：请见产品本体
产地：中国福建厦门

飞利浦家电（中国）投资有限公司
上海市静安区灵石路728弄20号201室
全国顾客服务热线：4008 800 008
本产品根据国标 GB4706.1-2005, GB4706.48-2009 制造

产品：飞利浦空气加湿器
型号：HU4813
额定电压：220V~
额定频率：50Hz
额定输入功率：25W
生产日期：请见产品本体
产地：中国江苏苏州

飞利浦家电（中国）投资有限公司
上海市静安区灵石路728弄20号201室
全国顾客服务热线：4008 800 008
本产品根据国标 GB4706.1-2005, GB4706.48-2009 制造

产品：飞利浦空气加湿器
型号：HU4816
额定电压：220V~
额定频率：50Hz
额定输入功率：18W
生产日期：请见产品本体
产地：中国江苏苏州

飞利浦家电（中国）投资有限公司
上海市静安区灵石路728弄20号201室
全国顾客服务热线：4008 800 008
本产品根据国标 GB4706.1-2005, GB4706.48-2009 制造