



Philips Design collection
Cordless phone with
answering machine

Leather

Black



ID9651B

A sense of luxury

Let your calling take on a whole new meaning with the ID965. Refinements such as the white-on-black display, the leather finished handset or the touch-sensitive keys will delight your senses and add this touch of luxury you deserve.

Exclusive design

- Leather finished handset
- Touch-sensitive keys on base
- Unique white-on-black display

Outstanding sound quality

- XHD sound
- Handset speakerphone allows you to talk handsfree

Never miss a call

- Direct access answering machine
- Up to 50 minutes recording time

Eco-designed

- Very low energy consumption
- Automatic reduction of the emitted power

PHILIPS
sense and simplicity

Specifications

Sound

- Handset ringers: Polyphonic
- Volume Control: Volume Control up/down

Picture/Display

- Backlight
- Backlight color: White
- Display colors: Black & White
- Lines of text: 3
- Main Display Technology: FSTN
- Main Display Type: Full graphic

Convenience

- Alarms: Alarm Clock
- Base Station keys: Answering machine keys, Paging key
- Battery charging indication
- Call Management: Call Waiting, Caller ID, Conference Call, Explicit Call Transfer, Microphone mute
- Ease of Use: Full Duplex Handsfree, Graphical User Interface, Keypad Lock, Menu Control
- Multi base capability: 1
- Multi handset capability: Up to 5 handsets
- Signal strength indication
- Backlit keypad: Yes (White)
- Speakerphone - talk handsfree

Network Features

- Antenna: Integrated on base, Integrated on handset

- Compatible: GAP
- Dialing: Tone, Pulse

Operator Requirements

- Name and Caller ID
- Caller ID on call waiting

Answering Machine

- Plug & Play Answering machine
- Recording time capacity: Up to 50 min.

Memory Capacity

- Call log entries: 50
- Phonebook: 200 names and numbers
- Redial List Capacity: 10

Dimensions

- Base dimensions: 163 x 84 x 20 mm
- Handset dimensions: 174 x 48 x 35 mm

Power

- Battery capacity: 750 mAh
- Battery type: AAA NiMH
- Kind of Battery: Rechargeable
- Mains power: AC 220-240V - 50Hz
- Number of batteries: 2 per handset
- Standby time: Up to 170 hours
- Talk time: Up to 14 hours

Highlights

Handset speakerphone

Handsfree mode uses a built-in loud speaker to amplify the voice of the caller, allowing you to speak and listen during a call without holding the phone to your ear. This is especially useful if you want to share the call with others or simply multitask.

XHD sound

No matter where you are, you can have a phone conversation that is free from noise, with incredible loudness and sound purity in the voice. Thanks to a high-quality speaker, sophisticated technology and to a real acoustic chamber, you can enjoy the unbelievable sound quality in every phone conversation.

Leather finished handset

The genuine leather finishing on the back of the handset adds the extra touch of luxury to an already exclusive design.

Touch-sensitive keys on base

No need to press hard on a key anymore; a light touch on a touch sensitive key suffice to register your input.

Unique white-on-black display

Apart from its fantastic appearance, the high contrast of a white-on-black display uniquely enhances readability.



Issue date 2012-03-04

Version: 6.0.7

12 NC: 8670 000 48194
EAN: 87 12581 45510 1

© 2012 Koninklijke Philips Electronics N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips
Electronics N.V. or their respective owners.

www.philips.com