



# Maximum Impact at Minimum Cost — Enduringly Economical!

- Low Cost of Ownership** Reduce your operating expenses with the bSure's unique long-life lamp, which last up to three times longer than conventional lamps!
- Extend Lamp Life** SmartSave™ extends valuable lamp life by automatically switching off the projector after a user-defined interval.
- Ultra-Quiet** Philips' innovative PAST™ system dramatically reduces fan noise to an ultra-quiet 27dB.
- Theft Deterrents** SecurityMax™ theft deterrent system and integrated Kensington lock protect your investment in any environment.
- Easy-to-Use** SmartSet™ utilizes advanced digital architecture to instantly adjust all display parameters for optimal performance and versatility.
- Future Proof** Featuring HDTVReady™ the bSure Series is fully compatible with future digital television standards.
- Now Even Brighter** The bSure Series delivers maximum impact with 1700 ANSI lumens light output.



Philips Multimedia Projectors



# PHILIPS



Model Name	bSure SV2	bSure XG2
Model Number	LC3132/27	LC3142/27
<b>LCD</b>	3x 0.7" high-temperature polysilicon active matrix LCD panels	
Native Resolution	SVGA (800x600)	XGA (1024x768)
Number of pixels	3x 480,000	3x 786,432
Brightness	1700 ANSI lumens	
Contrast	300:1	
<b>Fan Noise</b>	27 dB	29 dB
<b>Lamp</b>	132 watt UHP™ lamp	150 watt lamp
Average Lifetime	6000 hours	3000 hours
<b>Lens</b>	F1.8 - 2.2 f = 28.4 - 34 mm Manual Focus, Manual Zoom (1.9 - 2.3 :1) Projection Distance 60" - 374" (for image diagonal 40" - 200")	
<b>Input Compatibility</b>	Video NTSC 3.58 / 4.43 / PAL / SECAM S-Video (Y/C) Component Video Input: YCbCr, YPbPr, RGB HDTV Compatible: (480p, 720p, 1080i)	
Computer	Compatible with: VGA, SVGA, XGA, SXGA, Mac/PC Horizontal Scan Rate: 15 - 108 kHz Vertical Refresh Rate: 50 - 120 Hz Bandwidth: 140 MHz	
Plug and Play Compatibility	Display Data Channel: DDC 1/2B Microsoft® Windows®, 95/98/ME/2000/XP compatible	
<b>Input Connectors</b>	Component Video (R/Pri/Cr, G/Y, B/Pb/Cb: 3x RCA)	
Video	1x Composite Video (RCA) 1x S-Video (Y/C: mini-DIN)	
Computer	1x RGB Data (D15-pin)	
<b>Audio</b>	Stereo Audio (2x RCA)	
Video	1x Stereo Audio (3.5 mm stereo jack)	
Speaker	6 watts	
<b>Mouse Control</b>	USB (type A), PS/2 (mini-DIN)	
<b>Features</b>	SecurityMax™ theft deterrent system, Kensington Lock SmartSet™ automatic image quality optimization SmartSave™ auto-standby mode helps extend lamp life ColorTracking™ provides superior colorimetry for Video display Digital Zoom and Digital Freeze Digital Keystone correction with FitScreen optimization Connect an external computer monitor using supplied Y-Cable	
<b>Physical Specifications</b>	Product Dimensions (HxWxD) 4.25" x 9.25" x 13.2" (108 x 235 x 335 mm) Product Weight 8.1 lbs (3.7 kg)	
<b>Power consumption</b>	Operating Voltage 100 - 240 VAC, 50/60 Hz Operation / Standby 170 watts / 5 watts   210 watts / 5 watts	
<b>Temperature Range</b>	Operational +41 to +95 °F (+5 to +35 °C) Storage -13 to +158 °F (-25 to +70 °C)	
<b>FCC Rating</b>	Class B	
<b>Included Accessories</b>	Compact Remote Control, Power Cord, Lens Cap Combined VGA-USB Cable (59" / 1.5m), Audio/Video cable (79" / 2m) Scart to RCA Adapter (audio/video), D15-pin Y-Cable CD-ROM User Guide (UK, D, F, E, PT, NL I) Quick Setup Card (UK, D, F, E, PT, NL, I)	
<b>Optional Accessories</b>	LCA3116 132 watt Replacement Lamp for bSure SV2 LCA3118 150 watt Replacement Lamp for bSure XG2 LCA1120 Soft Carrying Bag LCA2211 Ceiling Mount	
<b>Model Number</b>	LC3132/27	LC3142/27

## Key Features


- Now with 1700 ANSI Lumens
- Long-life UHP™ Lamp (up to 6,000 hours)
- Ultra-Quiet Operation as low as 27dB
- Powerful 6-watt Speaker

## Projection Chart

Image Diagonal Size		Projection Distance			
		Tele Position		Wide Position	
[inch]	[meters]	[inch]	[meters]	[inch]	[meters]
40	1.0	74	1.9	60.3	1.5
60	1.5	112	2.8	91	2.3
70	1.8	130	3.3	106	2.7
80	2.0	150	3.8	121	3.1
100	2.5	187	4.7	152	3.9
150	3.8	280	7.1	228	5.8
200	5.1	374	9.5	304	7.7

All values are estimates

## Input Panel



## Hassle-Free Service and Support

Philips' First Choice Warranty assures you that you'll always be ready to present even in case of equipment failure thanks to our toll-free technical support (1 year), 48-hour Roadside Assistance Program and 3-year Parts and Labor Warranty.\*\*

INTERNET ADDRESS: <http://www.philipsusa.com>  
 TECHNICAL SUPPORT: Toll Free 1-888-873-4672  
 SALES INFORMATION: Toll Free 1-888-327-3636

Philips Consumer Electronics  
 64 Perimeter Center East  
 Atlanta, Georgia 30346

Design and specifications are subject to change without notice. Printed in the U.S.A., ©2003 Philips Consumer Electronics Co., a Division of Philips Electronics North America Corp.

\* Available in the USA and Western Europe. Check with your dealer for similar coverage in other regions.

\*\* Projector warranty is 3 years or 2500 hours, whichever comes first. Run time is kept by an internal clock.

Warranty on internal projection lamp is 12 months.

All trademarks are property of their respective owners.

CCM-150-2\_10/03

Literature Order Number: bSure /27 Series

