



Philips  
Network Laserfax with  
printer

LaserMFD 6080



LFF6080

## Simply your daily business

The new Philips Laser MFD 6080 combines several office routine jobs in one device - faxing, printing, scanning and copying with network connectivity. The laser technology saves up to 40% toner and the rco mode ensures efficiency.

### **Colour scanner**

- Optical resolution 600 x 2400 dpi

### **Eco mode for more efficiency**

- Saves up to 40% toner

### **Efficient laser printer**

- Prints up to 20 pages/min.

### **Flexible direct-USB**

- Direct print from USB stick

### **Network connectivity**

- Ethernet 10 Base T/ 100 Base TX

# PHILIPS

# Specifications

## Laser Fax

- Easy polling:: receive and send
- Error Correction Modus
- Fast fax transmission:: 2,5 sec. /page
- Fax Type:: G3
- ITU T30 standard/T30 new
- Memory:: up to 125 pages
- Name dial entries:: 250
- Predefined fax forms
- Printing resolution:: 600 dpi
- Sudoku printing with solutions: easy - medium - tough - devil
- 50 page automatic doc feeder
- Mailbox function
- Modem speed: 33,600 bps
- Page header

## Network laser printer

- Manual duplex print
- Paper tray: up to 250 pages
- Printing languages: GDI, PCL-6, PS3
- Printing resolution: 600 x 600 dpi
- Printing speed: 20 ppm

## Scanner

- Resolution: 4800 x 4800
- Optical resolution: 600 x 2400 dpi
- Scan to: FTP, Disk, mail

## Copier

- Grey scales: 64
- Zoom-function (enlarge/reduce)
- Multicopy: up to 99 pages
- Copy resolution:: 600 x 600 dpi
- Copy speed: 20 ppm
- ID-Card Copy function

## Direct USB

- Faxarchive
- Key-to-print via USB-Stick
- Scan-to-key via USB-Stick

## PC connection

- PC Interface USB 2.0
- WLAN-dongle: optional

## Accessories

- Philips PFA 821: cartridge with PLUG'N'PRINT card
- Philips PFA 822: long life cartridge with PLUG'N'PRINT card

## Power use

- Stand by: 17 W
- Eco mode: 13 W
- Operation: 340 W

## Dimensions

- Packed (WxDxH): 500x487x554 mm
- Unpacked: 412x447x386 mm

## Weight

- Packed (including country kit): 16 kg
- Unpacked (without accessories): 13 kg

## Temperature range

- Operation: 10°C to 32°C
- Storage packed: -20°C to 40°C

## Relative humidity

- Operation: 20% to 80%
- Storage packed: 20% to 80%

## Standard package includes

- CDs: 2 (incl manual)
- Device: incl mains cable
- Easy Install
- Starter Toner
- Warranty information

## Operating systems

- Linux
- Mac OS X: 10.3 to 10.5
- Vista x32
- Windows 2000 (>SP4)
- Windows XP (>SP1)
- x64 and Windows Server 2003: only for print

## Processor

- for Windows 2000: 800 MHz
- for Windows Vista and XP: 1 GHz

## RAM

- for Windows 2000: 128 MB
- for Windows Vista: 1 GB
- for Windows XP: 192 MB

## Features

- Printing method: Laser
- Monthly Fax volume: more than 50 pages
- Multifunctional product

# Highlights

## Direct print from USB stick

Direct print from USB stick

## Optical resolution

Optical resolution 600 x 2400 dpi

## Prints up to 20 pages/min.

Prints up to 20 pages/min.

## Saves up to 40% toner

Saves up to 40% toner

## Fast fax transmission

Fast fax transmission: 2,5 sec/page

## Ethernet

Ethernet 10 Base T/ 100 Base TX



Issue date 2014-02-12

Version: 2.0.1

12 NC: 8670 000 65873  
EAN: 34 25160 26268 1

© 2014 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)

\* Depends on the availability of the service on the local operators network

\*\* Depends on the availability of caller identification