



Philips  
Linea design cordless  
phone

1.6" display/ white backlight  
Handset speakerphone



M3301W

## The purest line to connect

Designed with simplicity and elegance in mind, the Philips LINEA takes pride of place in any modern home. Precisely engineered and crafted, as reflected in its timeless architectural silhouette, the LINEA truly is a desirable work of art.

### Outstanding design in high-quality execution

- Slender design and compact footprint for space efficiency
- Perfectly adjusted magnetic force ensures secure docking
- Calibrated keys for precise dialing
- Smart cable management maintains visual appeal at all angles
- Extra weight integrated in the base for greater stability

### Ultimate calling experience

- High contrast 4.1cm (1.6") 2-line reverse display
- Advanced sound testing and tuning for superb voice quality
- Handset speakerphone allows you to talk handsfree
- Save up to 50 favorite contacts in your phonebook
- Enjoy 16 hours of talk time on a single charge

### Eco-conscious product

- Zero power emission when ECO+ mode is activated

**PHILIPS**

Linea design cordless phone  
1.6" display/ white backlight Handset speakerphone

M3301W/53

# Highlights

## 4.1cm (1.6") reverse display



High contrast, white-on-black reverse LCD display ensures easy reading and also blends well with the overall sleek design language.

## 50-name phone book

Save up to 50 favorite contacts in your phonebook

## Calibrated keypad



The calibrated and carefully designed keypad ensures precise dialing where you clearly feel every keystroke whether you are dialing a number or entering a phonebook contact.

## Compact footprint



Slender design and compact footprint for space efficiency

## ECO+ mode



Philips phones are energy efficient and designed to be respectful to the environment. When ECO mode is activated the emitted radiation is reduced by up to 60%, and up to 95% when the phone is charging. With ECO+ mode activation the radiation drops to zero.

## Handset speakerphone



Handsfree mode uses a built-in loud speaker to amplify the voice of the caller, allowing you to speak and listen during a call without holding the phone to your ear. This is especially useful if you want to share the call with others or simply multitask.

## Perfect look from every angle



The smart cable management system cleverly hides the wires from sight. Intelligently designed concealed sockets and an internal


cable guide ensure everything is clutter free and neatly tucked away.

## Secure docking



Precisely adjusted magnets – with optimized force – are placed on the top of the handset and the base to ensure secure docking of the phone in a stable, upright position. A cleverly designed recess on the base not only serves as an attractive design highlight but also helps guide the user's hand for easy pick-up of the handset.

## Superb sound quality



HQ-Sound refers to high quality acoustic engineering that results in voice quality so crisp and natural it is almost like being there in person. High quality components, precise acoustic design, advanced testing and fine tuning reflect decades of experience in high end audio systems and headphones.

## Up to 16 hours talk time

Enjoy 16 hours of talk time on a single charge

## Weighted base for stability

Extra weight integrated in the base for greater stability

# Specifications

## Convenience

- Menu structure in the handset: List Menu
- Speakerphone - talk handsfree
- Signal strength indicator: 3-bar indicator
- Battery level indicator: 3-bar battery icon
- Intercom - multiple handsets
- Date / Time display
- Battery charge indication
- Signal strength indication
- Programmable hot keys: Key 1 and 2
- Call Management: Call Waiting\*, Caller ID\*, Microphone mute, Missed Calls, Received Calls
- Keypad lock
- Key tone on/off
- Auto hang up
- Multi base capability: 1
- Multi handset capability: Up to 4
- Backlit keypad: White
- Up to 16 hrs talk time
- Up to 180 hrs standby time
- Charge time: 8 hours
- Line cord length: 1.8m
- Power cord length: 1.8m
- Range: Open field <300m; in door <50m

## Sound

- Ringtones on handset: 10 polyphonic
- HQ-Sound

## Picture/Display

- Display size: 4.1cm / 1.6"
- Display type: 1-line dot matrix + 1-line numeric + hard icons
- Backlight: Yes
- Backlight color: White

## Memory Capacity

- Phonebook: 50 names and numbers
- Redial List Capacity: 10 entries
- Call log entries: 20 entries
- Phonebook store in the base

## Power

- Battery Capacity: 550 mAh
- Battery type: 2xAAA NiMH Rechargeable
- Mains power: AC 100-240V ~50/60Hz
- Power Consumption: < 0.7 W

## Security

- Transmission encryption : Yes

## Network Features

- Compatible: GAP

## SAR Value

- Philips handsets: <0.1 W/kg

## Eco Design

- Eco+

## Packaging dimensions

- Packaging type: Carton
- Number of products included: 1
- Type of shelf placement: Laying
- Packaging dimensions (W x H x D): 22.5 x 12 x 10 cm
- Gross weight: 0.5962 kg
- Nett weight: 0.4188 kg
- Tare weight: 0.1774 kg
- EAN: 48 95185 60110 6



Issue date 2022-04-24

Version: 5.0.4

12 NC: 8670 001 16618  
EAN: 48 95185 60110 6

© 2022 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)

\*\*This feature requires additional subscription of Caller ID service.  
Please check with your local network operator for details.