



Philips
Tablet

20.3cm/8" LCD
4GB
3G data



PI4010GB1

Live. Work. Play.

Fast, light and right for you wherever you go

Keep this lightweight Philips tablet by your side wherever you go. 3G connectivity, a vivid display for a more immersive viewing experience and a fast processor will keep you connected, productive and entertained everywhere.

Compact, versatile and ready for anything

- 3G connectivity for internet wherever you go
- 8" 1280x800 IPS TFT color LCD screen
- Featherlight and ultra compact for effortless handling
- Quad core 1.3GHz processor for fast & smooth user experience

Experience more with your tablet

- USB Audio with supported Philips Android docks
- USB OTG for connecting peripherals and USB flash drives

Reach out to the world from anywhere

- 2MP camera & front-facing VGA camera
- Built-in GPS for navigation, social networking and gaming
- High-speed Wi-Fi for fast internet access and app download
- Miracast™: Wirelessly unleash your tablet content on your TV
- Bluetooth® connectivity for connecting and sharing

PHILIPS

Tablet
20.3cm/8" LCD 4GB, 3G data

PI4010GB1/58

Highlights

Built-in GPS for navigation

Built-in GPS for navigation, social networking and gaming

2MP camera+front-facing camera

2MP camera & front-facing VGA camera

3G connectivity

3G connectivity for internet wherever you go

Featherlight and ultra compact

Featherlight and ultra compact for effortless handling

High-speed Wi-Fi

High-speed Wi-Fi for fast internet access and app download

Miracast™

Wirelessly unleash your tablet's content on your TV with Miracast™. Anything on your tablet screen can be viewed on your television in an instant. Look at photos, watch videos, stream YouTube, even play mobile games on your TV's big screen wirelessly.*

USB Audio with Philips Android

Dock the tablet to a Philips Android dock with USB audio support to play your favorite tunes from your tablet and charge at the same time.

USB OTG

USB On The Go support allows easy connection of USB peripherals including flash drives, digital cameras even a mouse or keyboard. It is ideal for making your tablet work harder for you.

Bluetooth®-enabled

Connect wireless devices including mouse and keyboard for more convenience, or easily share photos and videos content with friends.

Quad core 1.3GHz processor

Quad core 1.3GHz processor for fast & smooth user experience



Specifications

Picture/Display

- Diagonal screen size: 8 inch / 21.3 cm
- Resolution: 1280(w)x800(h)x3(RGB)
- Display screen type: IPS LCD display
- Display colors: 16 millions
- Aspect ratio: 16:10
- Multi-touch capacitive panel: 5 points
- Backlight

Sound

- Built-in speakers: Yes, Mono
- Output Power: 0.6W
- Frequency response: 20 - 20kHz (For headphone)
- Signal to noise ratio: > 70 dB(A)
- THD: 1% at 1kHz

Audio Playback

- MP3 bit rates: 8 - 320 kbps and VBR
- Compression format: MP3, 3GPP, AAC, AMR-NB, AMR-WB, FLAC, MIDI, Ogg Vorbis, WAV
- ID3 Tag support: Track title and artist name
- MP3 sample rates: 8, 11.025, 16, 22.050, 24, 32, 44.1, 48 kHz
- WMA bit rates: 5-192 kbps
- WMA sample rates: 8, 11.025, 16, 22.05, 32, 44.1, 48 kHz

Cameras

- Front facing camera: 0.3 MP
- Rear camera: 2 MP

Connectivity

- Wireless LAN: 802.11 b/g/n
- SD/MMC card slot: Micro SD card slot (Support up to 32GB)
- USB: High speed micro USB
- Headphone jack: 3.5mm Stereo Headphone
- DC in: 5V, 2A (Via Micro USB jack)
- 3G data connectivity: WCDMA 900/2100 HSDPA

Convenience

- Battery charging indication: On user interface
- Battery low indication
- Dedicated volume controls
- Firmware upgradeable
- G-sensor
- Superscroll
- Keypad lock
- Screen lock

Accessories

- AC/DC Adaptor: Input: AC 100-240V/0.5A, Output: DC 5V/2A
- Quick start guide
- USB cable: Yes, USB-Micro USB cable

Power

- Battery Type: Built-in battery, LI-Polymer
- Battery lifetime: Up to 8 hours
- Battery capacity: 4060mAh
- Rechargeable: Yes, via USB

Dimensions

- Product dimensions (W x H x D):

- 122 x 285 x 7.9 mm
- Product weight: 0.32 kg
- Packaging type: D-box
- Packaging dimensions (WxHxD): W292 x D156 x H27.5 mm

Audio Capturing

- Built-in microphone: mono
- Voice recording

Green Specifications

- Lead-free soldered product

Operating System

- Android 4.2 (Jelly Bean)

Still Picture Playback

- Picture Compression Format: BMP, GIF, JPEG, PNG
- Slide show

Storage Media

- Built-in memory (RAM): 1GB RAM, 4GB User memory
- Built-in memory type: NAND Flash

System Requirements

- Internet connection: Yes (For software upgrade and access to support document)
- PC OS: Windows XP (SP3)/ Vista/ 7
- Free USB port
- Windows Media Player: 11 or above

Preloaded Applications

- AccuWeather
- Blogger
- Books
- Camera
- Chrome browser
- Currents
- Deezer
- Docs/ Drive
- ES File explorer
- Gallery
- Gmail™
- Google Maps™
- Google Play store
- Google Search™
- Google Talk™
- Google Translate
- Google Voice search
- Google+
- Keep
- Movies
- Orkut
- Play music
- Web Browser
- YouTube™
- Earth
- Kingsoft Office

Outer Carton

- Gross weight: 4.93 kg
- GTIN: 1 48 95185 60079 3

- Outer carton (L x W x H): 60 x 60 x 60 cm
- Nett weight: 3.6 kg
- Number of consumer packagings: 10
- Tare weight: 1.33 kg

Packaging dimensions

- Packaging dimensions (W x H x D): 31.5 x 32 x 19.3 cm
- EAN: 48 95185 60079 6
- Gross weight: 0.46 kg
- Nett weight: 0.36 kg
- Number of products included: 1
- Packaging type: Carton
- Tare weight: 0.1 kg
- Type of shelf placement: Laying

Product dimensions

- Product dimensions (W x H x D): 30 x 18 x 31 cm
- Weight: 0.1 kg



Issue date 2016-08-02

Version: 2.2.3

12 NC: 8670 001 16351
EAN: 48 95185 60079 6

© 2016 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com

* Rechargeable batteries have a limited number of charge cycles and may eventually need to be replaced. Battery life and number of charge cycles vary by use and settings.
* Battery life varies by use and settings.
* Battery life of playtime is approximate and may vary depending on application condition. To optimize battery life, user should turn LCD backlight to minimum, connect to headphones (not built-in speakers) and listen at medium volume level, and use the product at room temperature.