



Philips PicoPix
Notebook pocket
projector

20 lumens

PicoPix



PPX1020

Project your life

The palm-sized and light Philips pocket projector can easily be connected to a PC via a USB port. This portable device allows you to share your photos, videos and documents at home or on the road.

High resolution

- Enjoy your pictures and films in SVGA resolution (800x600)

Large image projection

- Project an image up to 203 cm (80") in size

Quick and easy connection

- Powered from USB, image transferred from USB

PHILIPS

sense and simplicity

Specifications

Technology/optical

- Brightness: up to 20 lumens
- Contrast ratio: 500:1
- Display technology: VueG8* LCoS
- Focus: manual
- Integrated stand: for a 6° display angle
- LED light source lasts over: 20,000 hours
- Light source: RGB LED
- Native resolution: 800 x 600 pixels
- Screen distance: 0.2 m–3.0 m
- Screen size (diagonal): 13.2 cm–205.7 cm
- Autoswitch: 16:9 and 4:3

Supported resolutions/formats

- WXGA: 1280 x 768 (60 Hz)
- XGA: 1024 x 768 (60 Hz)
- SVGA: 800 x 600 (60 Hz)

Connection

- Mini USB 2.0

Power Supply

- USB powered

Dimensions

- Packed (W x D x H): 164 x 147 x 66 mm
- Unpacked: 88 x 88 x 25 mm

Weight

- Packed: 0.387 kg
- Unpacked (without accessories): 0.150 kg

Temperature range

- Operation: 5–40° C
- Storage packed: -25–60° C
- Storage unpacked: 0–45° C

Relative humidity

- Operation: 15–85% RH

- Storage packed: 5–93% RH
- Storage unpacked: 15–85% RH

Operating systems

- Windows XP (32-bit, 64-bit)
- Windows Vista (32-bit, 64-bit)
- Windows 7 (32-bit, 64-bit)

Minimum PC configuration

- CPU: Intel Pentium M 2 GHz or AMD Athlon 2 GHz above
- OS: Windows XP Professional SP2 32-bit
- Windows Vista: Home Premium 32-bit
- Windows 7: Home Premium 32-bit
- SDRAM: 1 GB DDR SDRAM
- USB interface: 2.0
- Free HDD space: 40 MB

Recommended PC configuration

- CPU: Intel Core 2 Duo 2.4 GHz or AMD Turion 64 X2 2.4 GHz above
- OS: Windows XP Professional SP2 32-bit
- SDRAM: 2 GB DDR SDRAM
- USB interface: 2.0
- Free HDD space: 80 MB

Prohibited CPU configuration

- Intel: Atom, Celeron
- AMD: Seperon
- VIA: C7

Standard package includes

- User guide
- Warranty card
- USB driver
- USB cable: (1 mini- 2 standard USB)
- Carrying case
- Tripod

Highlights

Large image projection

Project an image up to 203 cm (80") in size

SVGA resolution

Enjoy your pictures and films in SVGA resolution (800x600)

USB powered

Powered from USB, image transferred from USB

VueG8™



Issue date 2013-01-10

Version: 4.0.1

12 NC: 8670 000 72597
EAN: 34 25160 29273 2

© 2013 Koninklijke Philips Electronics N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips
Electronics N.V. or their respective owners.

www.philips.com

* patented all-digital smart panel technology by Syndiant