

# PHILIPS

## NORELCO

Do it yourself head  
groomer

Headroom

180° rotating head

corded & cordless



QC5550/40



## The best balder

Zero millimeter, 100% reach

A perfectly smooth and precisely shaved head with the Philips Norelco QC5550/40 do-it-yourself hair clipper.

### Easy to use

- 2-year guarantee, worldwide voltage.
- 100% waterproof for easy cleaning

### Shave or trim. Perfect results without help.

- Shave: Balder attachment for a smooth and precise shave
- 180° rotating head for 100% reach
- Adjustable zoom ring for easy length settings
- Contour-following combs for speed and comfort
- Skin-friendly blades and combs are gentle to the skin
- Quick Charge Power System: 1hr/60 minutes cordless use
- Fully washable for easy cleaning
- Includes hand-held mirror and storage pouch
- Corded and cordless use
- Battery charging, full and low indication
- Self-sharpening blades



reddot design award  
product design 2011

# Highlights

## Balder attachment




3. Shave your own head easily and comfortably. The balder attachment clips on and off easily and guarantees a smooth shave without the nicks and cuts that can be caused by blades.

## 180° rotating head




Makes trimming or shaving your own head easier than ever. Simply select the right angle to comfortably reach all parts of your head without help.

## Adjustable zoom ring




Easily select and set your desired hair length by turning the integrated zoom ring. The length settings are clearly visible on the side of the combs.

## 2D Contour-following comb



The 2D combs gently follow the contours of your head for a smooth, even and comfortable hair cut.

## Skin-friendly



Rounded edges on the blades and combs are designed to avoid scratching the skin for a more comfortable experience.

## Quick charge battery



The lithium-Ion battery is fully charged in 1 hour and provides constant power for up to 60 minutes cordless use.

## 100% Washable




Conveniently washes under the tap for a thorough clean.

## Includes mirror and pouch



The hand-held mirror provides extra visibility when trimming or shaving the back of your head. Safely keep together your product and attachments in the soft storage pouch.

## Corded and cordless use



For flexibility and convenience the headgroomer can be used with or without the power cord.

## Self-sharpening blades



The self-sharpening, stainless steel blades stay sharp longer and ensure top cutting performance.



## Red dot award design logo

Winner of Red dot award: product design 2011. Red dot for high design quality.

# Specifications

## Cutting system

Cutter width: 41 mm

Number of length settings: 11

Range of length settings: from 0 to 15 mm

Precision (size of steps): By 2mm mm

Comb type: Contour following

Balder attachment (0 mm)

Precision comb (1 to 3 mm)

Small comb (3 to 15 mm)

## Ease of use

Zoom wheel

Display: Charging indicator

Cleans under the tap

Adjustable guide combs

## Power system

Battery type: Li-ion

Charging time: 1 hour

Running time: 60 minutes

Usage: Corded/cordless

## Design

Shape: Ergonomic

## Accessories

Cleaning brush

Mirror

Storage pouch

2 guide combs

Balder attachment

## Service

2-year worldwide guarantee

